


# Reliable Hole Saw

with Allround Application



**New!** The HSS bimetal hole saw with standard adapter system.




**BOSCH**  
Invented for life

**High quality material**

The Bosch HSS bi-metal hole saw composes of HCS carrier and HSS teeth which provides extended lifetime.

**Multiple application:**

It cuts in metal,aluminium, plastic and wood.



**Special tooth geometry**

The vario-pitch tooth technology and improved gullets enable faster and smoother cutting.



**Broad range**

Complete range from 14mm to 152 mm, covers all important diameters.



**Standard adapter system**

It fits not only Bosch adapter but also most bimetal hole saw adapter systems in the market.



Diameter mm	Cutting Depth mm	Sales package quantity	Part number	EAN code
14	38	1	2608580396	3165140518185
16	38	1	2608580397	3165140518192
17	38	1	2608580398	3165140518208
19	38	1	2608580399	3165140518215
20	38	1	2608580400	3165140518222
21	38	1	2608580401	3165140518239
22	38	1	2608580402	3165140518246
24	38	1	2608580403	3165140518253
25	38	1	2608580404	3165140518260
27	38	1	2608580405	3165140518277
29	38	1	2608580406	3165140518284
30	38	1	2608580407	3165140518291
32	38	1	2608580408	3165140518307
33	38	1	2608580409	3165140518314
35	38	1	2608580410	3165140518321
37	38	1	2608580411	3165140518338
38	38	1	2608580412	3165140518345
40	38	1	2608580413	3165140518352
41	38	1	2608580414	3165140518369
43	38	1	2608580415	3165140518376
44	38	1	2608580416	3165140518383
46	38	1	2608580417	3165140518390
48	38	1	2608580418	3165140518406
51	38	1	2608580419	3165140518413
52	38	1	2608580420	3165140518420
54	38	1	2608580421	3165140518437
56	38	1	2608580422	3165140518444

Diameter mm	Cutting Depth mm	Sales package quantity	Part number	EAN code
57	38	1	2608580423	3165140518451
59	38	1	2608580424	3165140518468
60	38	1	2608580425	3165140518475
64	38	1	2608580426	3165140518482
65	38	1	2608580427	3165140518499
67	38	1	2608580428	3165140518505
68	38	1	2608580429	3165140518512
70	38	1	2608580430	3165140518529
73	38	1	2608580431	3165140518536
76	38	1	2608580432	3165140518543
79	38	1	2608580433	3165140518550
83	38	1	2608580434	3165140518567
86	38	1	2608580435	3165140518574
89	38	1	2608580436	3165140518581
92	38	1	2608580437	3165140518598
95	38	1	2608580438	3165140518604
98	38	1	2608580439	3165140518611
102	38	1	2608580440	3165140518628
105	38	1	2608580441	3165140518635
108	38	1	2608580442	3165140518642
111	38	1	2608580443	3165140518659
114	38	1	2608580444	3165140518666
121	38	1	2608580445	3165140518673
127	38	1	2608580446	3165140518680
140	38	1	2608580447	3165140518697
152	38	1	2608580448	3165140518703

06.09PT/SAZ1. Printed in Singapore. We reserve the right to change technical details without prior notice. No responsibility taken for printing errors.



**BOSCH**  
Invented for life

**Robert Bosch (SEA) Pte Ltd**

38C, Jalan Pemimpin,  
Singapore 577180  
Tel: (65) 6258 5511 Fax: (65) 6350 5315

For further enquiries, please contact

