BFS Scale: NTS Sheet 1/1	Aprvd Date 10/02/03 Aprvd By MC Drwn by	FOR MULTIPOLE CONNECTOR	
REF	CUSTOMER FILTER F	IERAL SPECIFICATION	DE TRON Components DE GUE
ALL DIMENSIONS IN MM	- CABLE SOCKET	TITLE PROFESSIONAL QUALITY	DrgNo 700-708-704-712 3 WAY
-		(22.08.97) IN JAN 2003	CONVERTED FROM PS00804 ISS4 (22.08.97)
1 giga-ohms	Insulation Resistance	708-0300 704-0300 712-033	3-Way 700-0300
3 milli-ohms	Contact Resistance	ck Nic	Deltron Part No Nickel
1500 Volts a.c.	Test Voltage	Silver Contacts Gold Contacts	Silver
4 pf 250 Volts a c	Cap. Between Contacts	(	
10 AWG 6.0 mm2	Maximum Wire Size (solid)		R (0"
16 Amps	Rated Current per Contact		
	Electrical Properties		
10N 5000	Withdrawal Force Min No. Insertions		
20N	Insertion Force		13.0
-30°C to +80°C	Operating Temp	5 max	68min / 71.5 max
Black, Brown, Red, Orange, Yellow, Green Blue Violet Grev White	Ident Options		
	Connector Ident		Dimensions
Spring-on coloured rings	Interchangeable		j -
Spring Steel, 3 m silver anti-tarnish	Screen		
Zinc high pressure diecasting	Screw Collar		
Acetal (UL 94 HB)	Chuck		
Santoprene (UL 94 HB)	Sealing Ring	grip.	- the strain relief collet ensures a positive cable grip
P.V.C. (black)	Strain Relief		non-latching connectors.
satin nickel or black chrome		mating smoothly with both lockable and	- a single piece latch which is simple to operate, mating smoothly with both lockable and
anu-tarnisn iinisn, or 0,5 m goid Zinc high pressure diecasting	I atch		movement occur between mating connectors.
Phos Bronze (pressed), 3 m silver	Contacts	ing mating, also ensuring a positive	- pressed socket contacts which 'lioat' to assist plug mating, also ensuring a positive
Valox DR48	Contact Base	nains applications)	(Note : these connectors are not to be used for mains applications)
Burner of the second right of the second sec	Greener	imple insert assembly.	- internal design features allow for a quick and simple insert assembly
Zinc high pressure diecasting	Housing		quick and easy system of channel identification.
Ø 2.8mm to Ø 8.0mm	Cable Range	vith a single number moulded in, offer a	- a range of coloured plastic coding rings, each with a single number moulded in, offer a
Chuck and Screw Collar	Cable Retention	a few quick turns of the back shell.	and disassembly is screw less and is achieved by a few quick turns of the back shell
	Mechanical Pronerties	ing many innovative features. Assembly	A range of audio & video connectors incorporating many innovative features. Assembly