

KNIPEX Pen-Style Control Cabinet Key and Profi-Key



- Practical pen-style with fastening clip
- Swivel-out key profiles
- Sturdy construction for versatile application



KNIPEX Quality - Made in Germany

Pen–Style Control Cabinet Key, for all standard cabinets and shut–off systems



Article No.	EAN-	Capaci	47			
	Code	'OI		-	Length	
	4003773-	mm	mm	Ømm	mm	g
00 11 07	063018	5/6/8	9	9	145	140

- easy to carry pen-style control cabinet key with fastening clip
- four different key profiles can be utilized by swivelling the key holder
- for control cabinets and shut-off systems in the supply of gas, water and electricity
- for technical installations in buildings, e. g. air conditioning and ventilation systems, shut-off valves, mains switch-boards, etc.
- ▶ female square 5; 6 + 8 mm
- ▶ triangular 9 mm
- two-way key bit 5 mm dia. (internal) / 9 mm dia. (external)

- KNIPEX
- universal 1/4" bit adapter for standard bits (permanent magnet for retaining)
- additional bit adapter for 1/4" bits inside one key profile
- with bit insert: cross recess PH 2 and possibility of safekeeping a second bit
- practical clip for safe transport
- corpus and fastening clip made from GRP plastic material; tool holder and key profiles zinc diecast



Opening a control cabinet with two-way key (Article No. 00 11 07)



Square for air bleeding (Article No. 00 11 07 + 00 11 08)



Tightening a screw with cross recess bit PH2 (Article No. 00 11 07 and 00 11 08)



Square in steps for opening a door without handle (Article No. 00 11 08)

Pen-style Profi-Key, for all standard shut-off systems



Article No.	EAN-	Capac	47			
	Code	'O			Length	
	4003773-	mm	mm	Ø mm	mm	g
00 11 08	063025	5 + 8	9	6/7/8/9	145	130

- easy to carry pen-style control cabinet key with fastening clip
- three different key profiles can be utilized by swivelling the key holder
- multi-purpose key for the builder
- key for heating, airconditioning, sanitary and building engineering, e. g. for door and window handles or for air bleeding heaters
- female square 5 + 8 mm
- ▶ triangular 9 mm

L100 01738/01/09.06/5.000/GB

male square in steps of 6 / 7 / 8 / 9 mm

- universal 1/4" bit adapter for standard bits (permanent magnet for retaining)
- ▶ additional bit adapter for 1/4" bits inside one key profile
- with bit insert: cross recess PH 2 and possibility of safekeeping a second bit
- practical clip for safe transport
- corpus and fastening clip made from GRP plastic material; tool holder and key profiles zinc diecast

Distributed by:

KNIPEX-Werk C. Gustav Putsch KG

Oberkamper Straße 13 42349 Wuppertal / Germany

Phone: +49(0)2 02/47 94-0 Fax: +49(0)2 02/47 74 94

Internet: www.knipex.de E-Mail: info@knipex.de