

My Book® Studio Edition™ II



Highlights

- Performance for creative pros
- Formatted for Mac
- RAID 1/0
- Quad interface
- User serviceable
- Works with Apple's Time Machine
- 5-year limited warranty

Copy

Short

WD's My Book® Studio Edition™ II dual-drive external storage system for Mac offers performance for creative professionals. Includes up to 2 TB of storage, RAID, quad-interface, user-serviceability, a 5-year limited warranty, and works with Apple's Time Machine.

Medium

WD's My Book® Studio Edition™ II dual-drive, quad-interface external storage system for Mac offers optimum performance for creative professionals. RAID enabled, this system comes configured for RAID 0 (striping) for extraordinary capacity and performance, or set it to RAID 1 (mirroring) for extra data protection. Includes automatic data backup software, user-serviceability, a 5-year limited warranty, and works with Apple's Time Machine.

Long

WD's My Book® Studio Edition™ II dual-drive, quad-interface external storage system for Mac offers optimum performance for creative professionals. Lightning-fast FireWire 800 or eSATA interfaces combined with RAID 0 (striping) yields the speed you need for fast, smooth video and audio editing, rendering complex 3D objects or special effects, and saving huge blocks of data in record time. Set the system to RAID 1 (mirroring) for the peace of mind in knowing that if one drive in this two-drive system ever fails, the system continues to run and your data is safe. Includes automatic data backup software, user-serviceability, a 5-year limited warranty, and works with Apple's Time Machine.

Ideal for

- Organize and archive vast photo and artwork libraries
- Edit and exchange massive audio and video projects
- Gain peace of mind with this true data guardian

Kit Contents

- Dual-drive storage system
- FireWire 800 cable
- FireWire 800 to 400 cable
- USB cable
- AC adapter
- Software CD
- Quick Install Guide

Compatibility

- Available USB, FireWire 800 or 400, or eSATA port or eSATA adapter card
- Mac OS® X 10.4.10+, 10.5.2+
- Windows® 2000/XP/Vista

Note: Compatibility may vary depending on user's hardware configuration and operating system.

My Book Studio Edition II

Product Specifications

Data transfer rate	
USB	480 Mb/s (maximum)
FireWire	800 Mb/s (maximum)
eSATA	3 Gb/s (maximum)
RoHS compliant ¹	Yes
Limited warranty ²	5 years

Product Dimensions

Height	6.54 in (166 mm) max.
Length	6.06 in (154 mm) max.
Width	3.87 in (98 mm) max.
Weight	5.2 lb (2.63 kg)

Power Specifications

AC input voltage	100 – 240V
AC input frequency	47 – 63 Hz

Environmental Specifications

Operating temperature	5°C to 35°C
Non-op. temperature	–20°C to 65°C

Packaging Specifications

	English	Metric
Retail box size	8.6 in. x 7.63 in. x 8.63 in.	217 mm x 194 mm x 219 mm
Retail box weight (max)	7.39 lb.	3.36 kg
Master carton size	15.6 in. x 8.9 in. x 9.3 in.	395 mm x 225 mm x 235 mm
Master carton weight	16.6 lb.	7.53 kg
Boxes per master carton	2	2
Master cartons per pallet	65	65
Pallet load weight	1128.77 lb.	512 kg
Pallet load size	48 in. x 40 in. x 51 in.	1219 mm x 1016 mm x 1302 mm

Note: Packaging may vary by region

Retail UPC Codes

PAN AMERICA			EUROPE/MIDDLE EAST/AFRICA		
Capacity ³	Order Number	UPC	Order Number	UPC	
1 TB	WDH2Q10000N	7 18037 72873 5	WDH2Q10000E	7 18037 72874 2	
1.5 TB	WDH2Q15000N	7 18037 72879 7	WDH2Q15000E	7 18037 72880 3	
2 TB	WDH2Q20000N	7 18037 72885 8	WDH2Q20000E	7 18037 72886 5	
ASIA			MULTI-CITY ASIA		
Capacity ³	Order Number	UPC	Order Number	UPC	
1 TB	WDH2Q10000A	7 18037 72875 9	WDH2Q10000S	7 18037 72876 6	
1.5 TB	WDH2Q15000A	7 18037 72881 0	WDH2Q15000S	7 18037 72882 7	
2 TB	WDH2Q20000A	7 18037 72887 2	WDH2Q20000S	7 18037 72888 9	

Note: Not all products may be available in all regions of the world.



For service and literature:

support.wdc.com
www.westerndigital.com

800.ASK.4WDC North America
949.672.7199 Spanish
+800.6008.6008 Asia Pacific
+31.20.4467651 EMEA

Western Digital, WD, the WD logo, and My Book are registered trademarks in the U.S. and other countries; and Studio Edition and the FIT Lab logo are trademarks of Western Digital Technologies, Inc. Other marks may be mentioned herein that belong to other companies. Product specifications subject to change without notice.

© 2008 Western Digital Technologies, Inc.
All rights reserved.

Western Digital
20511 Lake Forest Drive
Lake Forest, California 92630
U.S.A.

4879-705048-A00 Mar 2008

¹ WD complies with the Restriction of Hazardous Substances (RoHS) Directive 2002/95/EC of the European Parliament, which is effective in the EU beginning July 1, 2006. RoHS aims to protect human health and the environment by restricting the use of certain hazardous substances in new equipment, and consists of restrictions on lead, mercury, cadmium, and other substances.

² The term of the limited warranty may vary by region. Visit support.wdc.com for details.

³ One terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.