



19" front panels

Inquiry: 0 Article(s) chosen



Order number: 30219-104

[add to cart](#)



Downloads:


[CAD-Data in DWG Format](#)

Delivery quantity:

| Item | Qty | Description |
|------|-----|----------------------------|
| 1 | 1 | 19" blank panel, aluminium |


Technical data:

| Description | Height | H | D | X1 | X2 |
|------------------------------------|--------|----------|---------|----|----|
| 3 mm, Al anodised, cut edges plain | 3 U | 132.5 mm | 57.1 mm | | |

Notes:

- Please order 19" assembly kit separately

Für diese Zeichnung bestehen wir aus 6 (sechse) Blättern



GEZEICHNET 3021

- 1) AlMg 3 G22 DIN1783 3.3535.25 3.00 dick mit Folie
- 2) AlMg 1 F13 DIN1783 3.3315.24 3.00 dick E6/C-0(KEV1)

| Blatt | Blatt-Nr. | Blatt-Titel | Blatt-Größe | Blatt-Format | Blatt-Maßstab | Blatt-Position | Blatt-Bezeichnung |
|-------|-----------|----------------------------|-------------|--------------|---------------|----------------|-------------------|
| 1 | 113 | HE A B C | 265.90 | 190.40 | 37.70 | HE | A B C |
| 2 | 108 | LACKLERT BAL 7032 | 221.40 | 146.00 | 37.70 | A | |
| 3 | 109 | SCHWEIßSCHÜTTIMANTEN BLANK | 177.00 | 101.60 | 37.70 | B | |
| 4 | 105 | | 132.50 | 57.10 | 37.70 | C | |
| 5 | 102 | | 88.10 | 76.20 | 5.95 | | |
| 6 | 099 | | 43.60 | 31.70 | 5.95 | | |
| 7 | 30219-096 | 30219-097 | 30219-098 | | | | |
| 8 | | | | | | | |

| Projectname / User / Utilisation | | | | Oberfl. / Surface / T. de Surface | | Freimaß-Tol. ISO 2768 M | |
|----------------------------------|--|--|--|---------------------------------------|--|-------------------------|--|
| Pulttaehaese | | | | n | | Normbereich | |
| Maßstab / Scale / Echelle | | | | Material / Matière | | Anzahl | |
| 1:1 | | | | 1 | | Zu. Units | |
| Indr. / Modification | | | | Date | | Tol. mm | |
| SYM | | | | 18.12.1997 | | 0.5 (1) c 3 mm | |
| Name | | | | Name | | 0.3 (1) c 4 mm | |
| birma | | | | birma | | 0.2 (1) c 8 mm | |
| Benennung / Title | | | | Z.Nr. / Drawing No. / Nr. du document | | Intern. / Int. / Pg | |
| FPL 1HE 84TE | | | | 30219-096 | | 00001/011 | |
| Designation | | | | Intern. / Int. / Pg | | Status | |
| TAB. 1/2/3/4/5/6/HE | | | | 00001/011 | | 011 | |
| Gez. / Drawn / Des. | | | | Date | | Status | |
| 17.12.1997 | | | | 17.12.1997 | | 011 | |
| Ersatz für / replace / replace | | | | GLEICHE NR. / VDM 02.11.76 | | DS | |
| STEM | | | | 30219096 | | 30219113 | |
| NDI | | | | 30219096 | | 30219113 | |

