



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
2012	A	Released	JN	1/05/09	JWM	1/05/09	JWM	1/05/09
2073	B	Length Corrected	JN	09-17-09	JN	09-17-09	JN	09-17-09



**Physical Properties:**

- Length: 15' Straight Cord
- Conductor: Tinned copper wire /18AWG (0.12mm x 65 strands)
- Outer Diameter: 2.5 M/M
- Terminations:
  - One end, molded 3/8" (10mm) Male Snap. Fastener with two receptacles for banana plugs.
  - One end, solderless #8 Ring Terminal, to accept screw and hardware.

**Material & Finish:**

- Ring Terminal: Copper, Tint Plate
- Banana Jacks: Brass, Nickel Plate
- Snap Fastener: Steel, Nickel Plate

**Electrical Properties:**

- Banana Jacks to Ring Terminal: 1 ohm or less
- Male/Female Snap Fastener to Ring Terminal: 1 megohm + or - 10%



**Description:**

-A 15' straight common point ground cord for grounding Table Mat / Wrist Straps.

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
Jason Nash	1/05/09
CHECKED BY:	DATE:
Jeff McVicker	1/05/09
APPROVED BY:	DATE:
Jeff McVicker	1/05/09

DRAWING TITLE: Ccmmon Point Ground Cord			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC23795	14N9059.dwg	B
SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1	