

STREAM Coded MultiMedia Keyboard

G85-23000/-23010



Facts & Features

- Plug & Play. Requires no software installation or extensive installation procedure
- Ultra-silent. Whisper keystroke for particularly low-noise use.
- Ultra-flat, modern design with pleasant-to-touch keys
- Standard keyboard layout (incl. cursor and number block)
- 6 HotKeys for comfortable volume control and the most important Mediaplayer functions
- incl. adapter for PS/2 interface
- GS approval

Delivery volume

- 1 keyboard
- 1 PS/2-adapter
- 1 printed manual

Approvals

- CE, FCC, cURus, c-tick, GOST-R, UL, TÜV/GS

Operating system

- Microsoft Windows® XP, VISTA

System requirements

- USB or PS/2 interface

Technical data

- Number of buttons:
105 + 6 = european layout with Windows™ and additional keys
104 + 6 = international layout with Windows™ and additional keys
- Weight:
approx. 936 g (keyboard)
approx. 1368 g (with packaging)
- Dimensions in mm:
approx. 472 x 176 x 18 (keyboard)
approx. 485 x 255 x 63 (packaging)
- Storage temperature:
-20 °C to 65 °C
- Operating temperature:
0 °C to 40 °C
- Operating life of individual keys:
> 10 million operations
- Interface:
USB (PS/2 with adapter)
- Current Consumption:
typ. 15 mA
- Packaging unit:
6 keyboards per master carton
14 master cartons per pallet

Order description

<i>Order number</i>	<i>Housing colour</i>	<i>Number of buttons</i>	<i>Country version</i>	<i>EAN-Code</i>
G85-23000BE-0	grey	111	Belgium	4025112060601
G85-23000DE-0	grey	111	Germany	4025112059513
G85-23000EU-0	grey	110	US-English with € symbol	4025112060717
G85-23000FR-0	grey	111	France	4025112060625
G85-23000GB-0	grey	111	UK-English	4025112060618
G85-23000BE-2	black	111	Belgium	4025112060632
G85-23000DE-2	black	111	Germany	4025112059520
G85-23000EU-2	black	110	US-English with € symbol	4025112060724
G85-23000FR-2	black	111	France	4025112060649
G85-23000GB-2	black	111	UK-English	4025112060656
G85-23010BE	silver / black	111	Belgium	4025112064302
G85-23010CH	silver / black	111	Switzerland	4025112064319
G85-23010DE	silver / black	111	Germany	4025112064326
G85-23010ES	silver / black	111	Spain	4025112064333
G85-23010EU	silver / black	110	US-English with € symbol	4025112064340
G85-23010FR	silver / black	111	France	4025112064357
G85-23010GB	silver / black	111	UK-English	4025112064364
G85-23010IT	silver / black	111	Italy	4025112064371

(Possible country versions, other upon request.)

Cherry GmbH
Cherrystraße
91275 Auerbach/Opf.
Germany

Phone: +49 9643 18-0
Internet: www.cherry.de
www.cherrycorp.com

Sales: +49 1805 243779 (01805-Cherry)
E-Mail: sales@cherry.de
Fax: +49 9643 18-1545

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2008 Cherry GmbH, Last update: 07.08.2008_V02

