

Wire-Thread-Inserts



M	1.5 D	DIN 8140	
Nominal size	Diameter	VPE	Mftrs List No.
M 2 x 0.4	1,5 D	100	7302
M 2.2 x 0.45	1,5 D	100	7303
M 2.5 x 0.45	1,5 D	100	7304
M 3 x 0.5	1,5 D	100	7305
M 3.5 x 0.6	1,5 D	100	7306
M 4 x 0.7	1,5 D	100	7307
M 5 x 0.8	1,5 D	100	7308
M 6 x 1.0	1,5 D	100	7309
M 7 x 1.0	1,5 D	100	7310
M 8 x 1.25	1,5 D	100	7311
M 8 x 1.0	1,5 D	100	7312
M 9 x 1.25	1,5 D	100	7313
M 10 x 1.5	1,5 D	100	7315
M 10 x 1.25	1,5 D	100	7316
M 10 x 1.0	1,5 D	100	7317
M 11 x 1.5	1,5 D	100	7319
M 12 x 1.75	1,5 D	100	7321
M 12 x 1.5	1,5 D	100	7322
M 12 x 1.25	1,5 D	100	7323
M 12 x 1.0	1,5 D	100	7324
M 14 x 2.0	1,5 D	50	7325
M 14 x 1.5	1,5 D	50	7326
M 14 x 1.25	1,5 D	50	7327
M 14 x 1.0	1,5 D	50	7331
M 16 x 2.0	1,5 D	50	7334
M 16 x 1.5	1,5 D	50	7335
M 18 x 2.5	1,5 D	25	7336
M 18 x 2.0	1,5 D	25	7337
M 18 x 1.5	1,5 D	25	7338
M 20 x 2.5	1,5 D	25	7339
M 20 x 2.0	1,5 D	25	7340
M 20 x 1.5	1,5 D	25	7341
M 22 x 2.5	1,5 D	10	7342

M	1.5 D		DIN 8140
Nominal size	Diameter	VPE	Mftrs List No.
M 22 x 2.0	1,5 D	10	7343
M 22 x 1.5	1,5 D	10	7344
M 24 x 3.0	1,5 D	10	7345
M 24 x 2.0	1,5 D	10	7346
M 24 x 1.5	1,5 D	10	7347
M 26 x 1.5	1,5 D	5	7349
M 27 x 3.0	1.5 D	5	7350
M 27 x 2.0	1.5 D	5	7351
M 27 x 1.5	1.5 D	5	7352
M 28 x 1.5	1.5 D	5	7353
M 30 x 3.5	1.5 D	5	7354
M 30 x 2.0	1.5 D	5	7355
M 30 x 1.5	1.5 D	5	7356
M 33 x 3.5	1.5 D	5	7357
M 33 x 2.0	1.5 D	5	7358
M 36 x 4.0	1.5 D	5	7360
M 36 x 3.0	1.5 D	5	7361
M 36 x 2.0	1,5 D	5	7362
M 36 x 1.5	1,5 D	5	7363

UNC	1.5 D		DIN 8140
Nominal size	Diameter	VPE	Mftrs List No.
No. 2 x 56	1,5 D	100	8300
No. 4 x 40	1,5 D	100	8301
No. 5 x 40	1,5 D	100	8302
No. 6 x 32	1,5 D	100	8303
No. 8 x 32	1,5 D	100	8304
No. 10 x 24	1,5 D	100	8305
No. 12 x 24	1,5 D	100	8306
1/4 x 20	1,5 D	100	8307
5/16 x 18	1,5 D	100	8308
3/8 x 16	1,5 D	100	8309
7/16 x 14	1,5 D	100	8310
1/2 x 13	1,5 D	100	8311
9/16 x 12	1,5 D	50	8312
5/8 x 11	1,5 D	50	8314
3/4 x 10	1,5 D	25	8316
7/8 x 9	1,5 D	10	8318
1" x 8	1,5 D	10	8319
1.1/8"	1,5 D	5	8320
1.1/4"	1,5 D	5	8321
1.3/8"	1,5 D	5	8322
1.1/2"	1,5 D	5	8323

UNF	1.5 D	DIN 8140	
Nominal size	Diameter	VPE	Mftrs List No.
1/4 x 28	1,5 D	100	8325
5/16 x 24	1,5 D	100	8326
3/8 x 24	1,5 D	100	8327
7/16 x 20	1,5 D	100	8328
1/2 x 20	1,5 D	100	8329
9/16 x 18	1,5 D	50	8330
5/8 x 18	1,5 D	50	8331
3/4 x 16	1,5 D	25	8333
7/8 x 14	1,5 D	10	8335
1" x 12	1,5 D	10	8337
No. 4 x 48	1,5 D	100	8390
No. 6 x 40	1,5 D	100	8391
No. 8 x 36	1,5 D	100	8392
No. 10 x 32	1,5 D	100	8393
1.1/8"	1,5 D	5	8396
1.1/4"	1,5 D	5	8397
1.3/8"	1,5 D	5	8398
1.1/2"	1,5 D	5	8399

BSW	1.5 D	DIN 8140	
Nominal size	Diameter	VPE	Mftrs List No.
1/8 x 40	1,5 D	100	8341
3/16 x 24	1,5 D	100	8342
1/4 x 20	1,5 D	100	8343
5/16 x 18	1,5 D	100	8344
3/8 x 16	1,5 D	100	8345
7/16 x 14	1,5 D	100	8346
1/2 x 12	1,5 D	100	8347
9/16 x 12	1,5 D	50	8348
5/8 x 11	1,5 D	50	8349
3/4 x 10	1,5 D	25	8351
7/8 x 9	1,5 D	10	8353
1" x 8	1,5 D	10	8355

BSF	1.5 D	DIN 8140	
Nominal size	Diameter	VPE	Mftrs List No.
3/16 x 32	1,5 D	100	8362
1/4 x 26	1,5 D	100	8363
5/16 x 22	1,5 D	100	8365
3/8 x 20	1,5 D	100	8366
7/16 x 18	1,5 D	100	8367
1/2 x 16	1,5 D	100	8368
9/16 x 16	1,5 D	50	8369
5/8 x 14	1,5 D	50	8370
3/4 x 12	1,5 D	25	8372
7/8 x 11	1,5 D	10	8374
1" x 10	1,5 D	10	8376