



Mounted points

Schleifstifte
Meules sur tige
Muelas de corindón

Aluminium oxide / Aluminiumoxid / Oxyde d'aluminium / Óxido de aluminio

Pink / Rosa / Rose / Rosa

Shape W / Form W / Forme W / Forma W




For actual size shape reference see pages 121-124




Für genaue Größenformkennung siehe Seiten 121-124


Pour le gabarit grandeur nature, voir pages 121-124

Para la referencia a tamaño / forma real, véanse las páginas 121-124



W144	W145	W146	W152	W153	W154	W160	W162	shape/Form/Forme/Forma	
GHW14403PKM	GHW14503PKM	GHW14603PKM	GHW15203PKM	GHW15303PKM	GHW15403PKM	GHW16003PKM	GHW16203PKM	Part Nr	
3mm	3mm	3mm	5mm	5mm	5mm	6mm	6mm	d1	
6mm	10mm	13mm	6mm	10mm	13mm	6mm	10mm	l1	
3mm	3mm	3mm	3mm	3mm	3mm	3mm	3mm	d2	
105,000	105,000	105,000	105,000	80,850	70,000	81,370	68,400		
10	10	10	10	10	10	10	10		
51	51	51	51	51	51	51	51	IPC Code	

W163	W164	W170	W175	W176	W177	W178	W179	shape/Form/Forme/Forma	
GHW16303PKM	GHW16403PKM	GHW17003PKM	GHW17503PKM	GHW17603PKM	GHW17706PKM	GHW17806PKM	GHW17906PKM	Part Nr	
6mm	6mm	8mm	10mm	10mm	10mm	10mm	10mm	d1	
13mm	19mm	13mm	10mm	13mm	19mm	25mm	32mm	l1	
3mm	3mm	3mm	3mm	3mm	6mm	6mm	6mm	d2	
60,000	45,900	55,000	54,000	45,370	66,000	55,200	45,000		
10	10	10	10	10	10	10	10		
51	51	51	51	51	51	51	51	IPC Code	

W182	W185	W186	W187	W188	W189	W196	W197	shape/Form/Forme/Forma	
GHW18206PKM	GHW18506PKM	GHW18606PKM	GHW18706PKM	GHW18806PKM	GHW18906PKM	GHW19606PKM	GHW19706PKM	Part Nr	
13mm	13mm	13mm	13mm	13mm	13mm	16mm	16mm	d1	
3mm	13mm	19mm	25mm	38mm	50mm	25mm	50mm	l1	
6mm	6mm	6mm	6mm	6mm	6mm	6mm	6mm	d2	
73,460	61,500	51,000	40,000	30,370	24,000	35,250	21,000		
10	10	10	10	10	10	10	10		
51	51	51	51	51	51	51	51	IPC Code	