

LOC		DIST		REVISONS			
GP	00	F	LTR	DESCRIPTION	DATE	DWN	APVD
		G		ADDED: -3 PER EC 0S15-0326-02	12SEP2002	DLD	RPM
		H		REVISED PER EC 0S15-0450-02	21JAN2003	DLD	RPM
		J		REVISED PER EC 0S15-0324-03	01DEC2003	JB	CF
		K		REVISED PER EC 0S15-0339-03	01DEC2003	JB	CF






⚠ MATERIAL: BASE - HIGH TEMPERATURE MOLDING COMPOUND, BLACK.
WIRE STUFFER: - HIGH TEMPERATURE MOLDING COMPOUND.
TERMINAL - COPPER ALLOY, PLATED WITH 3.81µm MINIMUM THICK
TIN OVER 1.27µm MINIMUM THICK NICKEL UNDERPLATE.

⚠ EACH WIRE ENTRY HOLE ACCEPTS ONE UNSTRIPPED SOLID COPPER
22-26 AWG WIRE WITH WIRE INSULATION DIAMETER RANGE FROM
.060 THROUGH .040. OTHER WIRE SIZES AND TYPES SHALL BE
SUBMITTED TO AMP ENGINEERS FOR APPLICATION APPROVAL.

3. SOLDER TABS PROVIDED FOR PERMANENT BOARD MOUNTING.

⚠ LOCATION OF HOLE PATTERN DETERMINED BASED ON CUSTOMER
REQUIREMENTS.

⚠ T AND R DESIGNATIONS NOT ON TAN STUFFER FOR 1339222-3.
OR 1339222-4



-	-	CLEAR	1339222-4
-	-	TAN	1339222-3
RED	GREEN	CLEAR	1339222-2
RED	GREEN	TAN	1339222-1
R	T	WIRE STUFFER	PART NUMBER
COLOR CODE			

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS TO BE USED TO MANUFACTURE THE PRODUCT AND THE CONTROLLING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN K. ZARBOCK 05OCT99	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK M. DERSTINE 05OCT99	NAME ASSEMBLY, SINGLE PAIR, SINGLE ENTRY, PIVOT II CONNECTOR	
TOLERANCES, UNLESS OTHERWISE SPECIFIED: 		APVD M. DERSTINE 05OCT99	PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING	
MATERIAL 		FINISH -	CAGE CODE A1 00779	DRAWING NO. C-1339222
			SCALE 8:1	SHEET 1 OF 1 REV K