



FOR FINISH DETAILS SEE 300816

PRODUCT CODE	L	GRIP RANGE
TAPD 603 BS	6.5	– 2.4
TAPD 604 BS	7.5	2.4 – 3.2
TAPD 606 BS	9.2	3.2 – 4.8
TAPD 607 BS	10.0	– 5.6
TAPD 608 BS	11.0	4.8 – 6.4
TAPD 610 BS	12.7	6.4 – 7.9
TAPD 612 BS	14.7	7.9 – 9.5
TAPD 614 BS	16.5	9.5 – 11.1
TAPD 616 BS	18.0	11.1 – 12.7
TAPD 617 BS	19.0	11.1 – 13.5
TAPD 625 BS	25.5	13.5 – 19.8
TAPD 633 BS	32.0	19.8 – 26.2

SHEAR STRENGTH 2020N	TENSILE STRENGTH 2800N	HOLE SIZE Ø 4.9/5.0			
MATERIAL MANDREL GALVANISED CARBON STEEL BODY EN573-3ALUMINIUM:EN AW-5154A (AlMg3.5%)		21NOV08	20585	14	RE
		30SEP04	19468	13	RE
This drawing is the property of Tucker Fasteners Ltd. It is confidential and must not be lent or copied except by written consent.	TITLE ALUMINIUM ALLOY 'POP' OPEN RIVET 6 SIZE DOMED HEAD GALVANISED MANDREL	22JUN04	19382	12	RE
		29SEP03	19135	11	RE
		ECN DATE	ECN No	ISSUE	APPROVED
ALL DIMENSIONS ARE IN MILLIMETRES		SCALE 3:1		DR GJ	Date 7/94

SHEET 1 OF 3		© TUCKER FASTENERS Ltd. EMHART TEKNOLOGIES Walsall Road, Birmingham B42 1BP A StanleyBlack&Decker, Inc. Company		DRAWING No.	
A4OPEN	A4			300920	