

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT	WIRE SIZE	DIMENSIONS in.					
PART NUMBER		±.03 <b>A</b>	B DIA.	±.003	±.01 DIA.		
BS22	26-22	.47 (11.9)	.08 (2.0)	.02 (0.5)	.04 (1.0)		



## NOTES:

- I. UL LISTED AND CSA CERTIFIED FOR:
   A. #26-22 AWG SOLID OR STRANDED
   COPPER WIRE
   B. 302° F (150° C) MAX. TEMP. RATING
- 2. MATERIAL:
  A. .02 (0.5) THK COPPER,
  TIN PLATED
- 3. See www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE
- 4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- 5. INSTALLATION TOOLS: CT-100 POCKET B
- 6. WIRE STRIP LENGTH: 9/32 +1/32 (7.1 +.8 -0)



04	4/11	SB		ADDED PACKAGING NOTE #3				CORP. TINLEY PARK, ILLINOIS	
03	1/01	RM		FILESPEC WAS N41336_PCD_02				CORP. TINLEY PARK, ILLINOIS	
02	12/94	ТН		UPDATED NOTES AND DIMENSIONS	02709			#26-22 BARREL NON-INSULATED	
l	9-88	DW		REDRAWN WITH REVISIONS				BUTT SPLICE	
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	РМ	DAW CHK'D SCALE NONE PRAWING NO. A41336	