

CATALOG

Soft Shell Connectors

↳ .163" Centerline, 600 V, 9.5 A max. (Mini Universal MATE-N-LOK)

**AMP** 172329-1 [Active](#)

**Directive 2002/95/EC Compliant**

[RoHS Compliant](#)

(Tyco Electronics P/N: 172329-1)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>▷ <a href="#">General Info</a></li> <li>▷ <a href="#">Sales Info</a></li> <li>▷ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>▷ <a href="#">Pricing</a></li> <li>▷ <a href="#">Product Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>▷ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

**Searchable Features:**

<b>Brand:</b>	AMP
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Product Type:</b>	Housing
<b>Connector Line:</b>	Mini-Universal MATE-N-LOK
<b>Number of Circuits:</b>	3
<b>Centerline, Matrix (mm [in]):</b>	4.14 [.163]
<b>Contact Layout:</b>	In-Line
<b>Housing Type:</b>	Receptacle (Cap)
<b>Mount:</b>	Panel Mount
<b>Gender:</b>	Receptacle (Cap)
<b>Packaging Method:</b>	One Piece Housing

**Other Properties:**

<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>Contact Diameter (mm [in]):</b>	0.99 [0.039]
<b>Voltage (VAC):</b>	600
<b>CompactPCI:</b>	No
<b>Housing Flammability Rating:</b>	UL 94V-2

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

<b>Housing Material:</b>	Nylon
<b>Color:</b>	Natural
<b>Lock Type:</b>	Positive Lock

[Copyright](#) and [Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]

