








2			1						
LOC HB	DIST	REVISIONS							
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD	
			C	REVISE VDE MARING AND LOT NO.	ECO-07-001278	2-JAN-07	KS.L	W.Y	
			D	CHANGE NEW LOGO	ECO-08-020477	13-FEB-09	D.L	BH.Y	
			D1	REVISION UPDATE ONLY	ECO-09-018236	27-AUG-09	D.L	BH.Y	



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			DWN Yang.Xiao		 Tyco Electronics Corporation Shenzhen, China					
			CHK N.Funayama							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±	APVD HSU,CHIEN-HUI		NAME OMIH(1T) D/L CUSTOMER DRAWING					
			PRODUCT SPEC							
			APPLICATION SPEC							
			WEIGHT							
			CUSTOMER DRAWING							
MATERIAL SEE MATERIAL TABLE		FINISH	SIZE A3		GAGE CODE 00779		DRAWING NO C- 5-1419121-9		RESTRICTED TO	
					SCALE 4:1		SHEET 1 OF 2		REV D1	

LOC HB	DIST	REVISIONS						
		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

NOTES:
1.LOT NO. SYSTEM AS FOLLOWING:

0

8

2

5

WEEK

YEAR

2.GENERAL TOLERANCE AS FOLLOWING:

TOLERANCE	
0~0.99mm	±0.1
1mm~2.99mm	±0.2
3mmMIN.	±0.3

④ 3.TERMINAL DIMENSION IS NOT INCLUDING SOLDER TIP.

7-1440000-6	OMIH-SH-148L	OMIH-SH-148L	48V
0-1440007-7	OMIH-SH-124L	OMIH-SH-124L	24V
5-1419121-9	OMIH-SH-112L	OMIH-SH-112L	12V
1-1419145-7	OMIH-SH-112D	OMIH-SH-112D	12V
TE PART NO	DESCRITION	PART A	PART B

RELAY TYPE