



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398




DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1861	A	RELEASED	BYF	11/05/05	HO	11/7/05	JWM	11/7/05



RoHS
Compliant

Specifications:

- Rated Current: 1A
- Max. Overload Current: 2A
- Max. Resistance: 50mΩ
- Insulation Resistance: 1,000 MΩ or More
- Dielectric-Withstanding Voltage: Apply 100 VAC between protective coating and termination for 1 minute.
- Solderability: 245°C±3°C, 2~3 seconds 95 % Coverage Min.



DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
BASAM YOUSIF	11/05/05
CHECKED BY:	DATE:
HISHAM ODISH	11/7/05
APPROVED BY:	DATE:
JEFF MCVICKER	11/7/05


DRAWING TITLE:

RoHS Compliant Thick Film Chip Resistors, EIA Size 0402, 1/16 Watt, 0 ohm

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-676	TA-676.DWG	A
SCALE: NTS		U.O.M.: Millimeters	SHEET: 1 OF 2



Tape & Reel Dimension



Multicomp Type No	Resistance	Package
MC0402WG00000TCE-TC	0 Ohm	Sold by Each
MC0402WG00000TCE-TR		Sold in Tape & Reel of 5,000