





注記
NOTE

- 端回路リブ付き
RIB STICK TO END CIRCUIT
- () 内寸法は参考値とする。
() DIMENSION IS FOR REFERENCE
- P.C. BOARD端面から基板穴までの距離
LENGTH FROM P.C. BOARD HOLE TO EDGE

ハウジング (ナイロン66、UL94V-2)
HOUSING (NYLON 66, UL94V-2)基板取付穴推奨寸法
RECOMMENDED PC BOARD HOLE DIMENSION

5と6の間 BETWEEN 5 AND 6	5と6の間 BETWEEN 5 AND 6	5と6の間 BETWEEN 5 AND 6	5と6の間 BETWEEN 5 AND 6	5と6の間 BETWEEN 5 AND 6	5と6の間 BETWEEN 5 AND 6
55.44 ^{+0.3}	59.3	26-01-1156	5145-15AH	15	
43.56 ^{+0.25}	47.42	-1126	-12AH	12	
39.6 ^{+0.25}	43.46	-1116	-11AH	11	
35.64 ^{+0.25}	39.5	-1106	-10AH	10	
31.68 ^{+0.2}	35.54	-1096	-09AH	9	
27.72 ^{+0.2}	31.58	-1086	-08AH	8	
23.76 ^{+0.2}	27.62	-1076	-07AH	7	
19.8 ^{+0.2}	23.66	-1066	-06AH	6	
15.84 ^{+0.15}	19.7	-1056	-05AH	5	
11.88 ^{+0.15}	15.74	-1046	-04AH	4	
7.92 ^{+0.15}	11.78	-1036	-03AH	3	
3.96 ^{+0.1}	7.82	26-01-1026	5145-02AH	2	
中央フック位置 CENTER HOOK	B	(A)	PART. NO.	ENG. NO.	極致 NO. OF CKTS.

角度 ANGLE	公差 TOLERANCE	記号 LTR	変更 REVISION	変更内容 REVISION RECORD	DR. CHK.	日付 DATE
30°以上 OVER	+0.3	K	変更 REVISED	(JC80184)	S.N.	97/09/02
10°以上 30°未満 OVER UNDER	+0.25	J	再作図 REDRAWN	(JC70319)	S.A.	96/05/24
10°未満 UNDER	+0.2				M.F.	
一般公差 GENERAL TOLERANCES						

材料/ハウジング: ナイロン66、UL94V-2 MATERIAL HOUSING: NYLON 66, UL94V-2	ターミナル: 黄銅、銅下付錫メッキ TERMINAL: BRASS, TIN OVER COPPER PLATE 0.254t
仕上げ FINISH	適用電線範囲 WIRE RANGE
被覆外径 INS. RANGE	被覆外径 INS. RANGE
DRAWN BY: 96/05/24 CHK'D BY: 97/09/02 S. ANDO Y. MIZUNO	APP'D BY: 97/09/02 M. FUKUSHIMA
尺度 SCALE	尺度 SCALE

MOLEX JAPAN CO., LTD.
日本モレックス株式会社
REVISE ONLY ON CAD SYSTEM
TITLE 名称
KK3.96 SOLDER
REC. HSG. ASSYDWG. NO.
SD-5145-NAHREV
K