

MATERIAL NUMBER	# OF COLUMNS	DIM "A" MAX	DIM "B"
75710-*005	5	18.50	14.80
75710-*006	6	22.20	18.50
75710-*008	8	29.60	25.90
75710-*010	10	37.00	33.30

75710-*0**

MODULE TYPE -- TAIL PLATING TYPE

UNGUIDED -- TIN/LEAD = 0

UNGUIDED -- TIN ONLY = 1




OF COLUMNS

05 = 5 COL

06 = 6 COL

08 = 8 COL

10 = 10 COL



DAUGHTERCARD HOLE PATTERN
(CONNECTOR SIDE)

NOTES:

1. MATERIALS: HOUSING - LIQUID CRYSTAL POLYMER (LCP) GLASS-FILLED, UL94V-0
TERMINALS - HIGH PERFORMANCE COPPER ALLOY
2. FINISH: 30 μ IN MIN GOLD IN CONTACT AREA. SELECTIVE TIN/LEAD (-0***)
OR SELECTIVE TIN (-1***) ON PCB TAILS. NICKEL OVERALL.
3. REFER TO MOLEX PRODUCT SPEC PS-75710-999 FOR PERFORMANCE SPECIFICATIONS.
4. PRODUCT IS PACKAGED PER PK-70873-609.
5. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.

REVISE NOTES EC NO: UCP2007-2348 DRW:BP1SZCZOR 2007/03/19 CHKD: 2007/03/19 APPR: JLAURX 2007/03/19	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY JLAURX DATE 09/01/2005		TITLE I-TRAC DAUGHTERCARD 11 ROW SIGNAL MODULE UNGUIDED SALES DWG			
			4 PLACES	± ---	± ---	CHECKED BY NMARTIN DATE 09/01/2005					
			3 PLACES	± ---	± ---	APPROVED BY CBIXLER DATE 09/01/2005					
			2 PLACES	± 0.13	± ---	MATERIAL NO.					
			1 PLACE	± 0.25	± ---			MOLEX INCORPORATED		DOCUMENT NO. SD-75710-001	SHEET NO. 1 OF 1
			ANGULAR ±1/2°			SEE CHART					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

SEE CHART

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION