


10 9 8 7 6 5 4 3 2 1

CKT	PART NO
80	87613-8012
80	87613-8013



NOTES:

1. MATERIALS:

HOUSING- NYLON 4/6 45% GF, COLOUR: BLACK
TERMINAL- PHOSPHOR BRONZE
METAL LATCH- STAINLESS STEEL

2. PLATING:

0.76um/30u" MIN GOLD IN CONTACT AREA,
TIN IN SOLDER AREA,
BOTH OVER NICKEL OVERALL

3. CARD SLOT ACCEPTS $(1.27^{+0.10}_{-0.08}) / .050^{+0.004}_{-0.003}$ P.C. BOARDS
(MEASURED OVER P.C. PADS).

4. PRODUCT SPEC PS-87613-100 APPLIES


5. CENTER PEG IS AN INTERFERENCE FIT TO PCB UNLESS NOTED
ON THE DWG.
(APPLICABLE ONLY IF PART HAS A CENTER PEG FEATURE)

6. MODULE WITH COMPONENT MUST NOT WEIGH MORE THAN 32 g.

7. OPTION 87613-8013 HAS A SMALLER TERMINAL GAP FOR MODULE
BOARD FITTING.


GAP: 87613-8011/8012 (1.04 ± 0.06)
87613-8013 (0.98 ± 0.06)

8. PARTS SHALL BE PACKED IN MOISTURE BARRIER BAG.




END VIEW
SCALE 4:1

RECOMMENDED SOCKET
P.C. BOARD HOLE PATTERN



$\phi (3.18 \pm 0.05) (X2)$
 $.125 \pm .002$

SIMM P.C. BOARD LAYOUT



ADD MOIST. BAG NOTE		QUALITY SYMBOLS	DESCRIPTION
EC NO: S2008-0548	2008/02/05		
DRWN:SKANG	2008/02/06	▽=0	
CHKD:ATSEE	2008/02/06	▽=0	
APPR:MLONG	2008/02/12		
B1	REV		

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± .010
2 PLACES ± 0.25	± .015
1 PLACE ± 0.38	± ---
ANGULAR ± 1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
KSEE	1999/05/11
CHECKED BY	DATE
PTL IM	2000/07/07
APPROVED BY	DATE
SKTOH	2000/07/07
MATERIAL NO.	
SIZE	
A3	

SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
TITLE SINGLE ROW METAL LATCH VERT.SIMM SOCKET 80 CKTS STANDARD ROTATION		
MOLEX INCORPORATED		
DOCUMENT NO. SD-87613-010		SHEET NO. 1 OF 1