

4 3 2 1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	REVISED PER ECO-11-005294	02APR11	RK	HMR

ACCESSORIES PREFIX "Z"	ITEM NO	DESCRIPTION OF ACCESSORY	1	2	3	4	5	6	7	8	9
5	5	BUSHING WITH THROUGHHOLE 3,1 DIA.									
5	5	BUSHING WITH THREAD 4-40 UNC		2						2	
5	5	BUSHING WITH THREAD M3			2						2
4	4	FEMALE SCREWLOCK WITH THREAD 4-40 UNC				2					2
4	4	FEMALE SCREWLOCK WITH THREAD M3					2				2
6	6	BOARDLOCK		2	2	2	2				

HOW TO ORDER:

37 POS. -----> Z-338316-Y

PREFIX FOR ACCESSORIES }
 BASIC PARTNR. }
 SUFFIX FOR PLATING }

PLATING SUFFIX "Y"

GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652)
 SOLDER-PART :TIN-PLATING 3µm.

-Y = -2

1 GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD; WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.

2 CAVITY IDENTIFICATION AT FRONT SIDE ONLY.

3 PARTNUMBER AND DATE CODE.

4. WHEN BOARDLOCKS ARE USED, CONNECTOR CAN BE USED FOR PCB THICKNESS OF 1,6 mm ONLY.

5. AIR AND CREEPAGE DISTANCES ACCORDING TO DIN 41652

ITEM NRS./MATERIAL :

1 SHELL = BRIGHT TINPLATED STEEL

2 HOUSING = GLASSFILLED POLYESTER, COLOR : BLACK

3 CONTACTS = PHOSPHORBRONZE (PLATING : SEE TABLE ABOVE)

4 FEMALE SCREWLOCK = TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3)

5 BUSHING = TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3 OR 3,1 DIA. THROUGHHOLE)

6 BOARDLOCK = TINPLATED PHOSPHORBRONZE

7 STAND OFF = ULTRAMID VO COLOR : BLACK

RECOMMENDED P.C. BOARD HOLE-LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	01JUL97	TE Connectivity	
		CHK	09SEP97	HDP-20 SIZE 4 VERTICAL+ RECEPTACLE HEADER; WITH SOLDER CONTACTS	
		APVD	09SEP97	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
		PRODUCT SPEC		A2 00779 C=338316	
		APPLICATION SPEC		SCALE SHEET 1 OF 1 REV F1	
		WEIGHT		CUSTOMER DRAWING	

1471-9 (3/11)