

X88590-V7

**MICRO SWITCH**  
a Honeywell Division

FED. MFG. CODE 91929

**SWITCH - BASIC**

CATALOG LISTING

**V7-5F17D8-336**  
CW-C5007

V7-5F17D8-336

CATALOG LISTING



ISSUE

5

REPLACES

PR-17737

PAGE 1 OF 1

REVISIONS

A	CO-94018	27 JAN 12
G R T		
27 SEP 99		
B	0085964	27 JAN 12
SBH		
27 JAN 12		

CHECK

27 JAN 12

CMH

CHECK


27 SEP 99

SAV

CHECK

27 SEP 99

GRT



NOTES

- 1 ALL CHARACTERISTICS TAKEN WITH SWITCH MOUNTING SURFACE HORIZONTAL
- 2 - THE MASS OF THE LEVER MAY PREVENT PLUNGER FROM RETURNING THE LEVER TO FREE POSITION
- 3 - CAUTION: OVERTRAVEL FORCE ON LEVER MUST NOT RESULT IN AN OVERTRAVEL FORCE ON PLUNGER EXCEEDING ONE OUNCE

~~ANSI Y14.5M-1982 APPLIES~~

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS

OPERATING FORCE	— — 2.3 GRAM MAX
DIFFERENTIAL TRAVEL	— — .100 MAX
OVERTRAVEL	— — .300 MIN
RELEASE TRAVEL	— — .056 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T

3A 125, 250, 277 VAC L163  
1/10HP 250 VAC



SCALE NONE DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE (.0)	±.030	
TWO PLACE (.00)	±.015	
THREE PLACE (.000)	±.005	
ANGLES	±	

WEIGHT

PTC/CAD 2D

DRAWN

27 SEP 99