

Technical drawing of a mechanical part, showing a top view and a side view. The drawing includes dimensions in millimeters (mm) and inches (in).

Top View Dimensions:

- Overall width: 40.8 mm (1.606 in)
- Overall height: 42.0 mm (1.654 in)
- Top flange width: 30.0 mm (1.181 in)
- Top flange height: 2.5 mm (.098 in)
- Central hole diameter: $\varnothing 13.0$ mm (.512 in)
- Central hole position from top edge: 18.5 mm (.728 in)
- Bottom flange width: 30.0 mm (1.181 in)
- Bottom flange height: 3.3 mm (.130 in)
- Overall bottom width: 55.0 mm (2.165 in)
- Bottom flange position from bottom edge: 7.5 mm (.295 in)

Side View Dimensions:

- Overall height: 6.5 mm (.256 in)
- Central hole diameter: $\varnothing 11.0$ mm (.433 in)
- Overall width: 46.50 mm (1.831 in)

