NOTES:	THIRD ANGLE PROJ. 🕀 🖯 REVISIONS
1. MATERIALS AND FINISHES:	REV DESCRIPTION DATE ECO APPR
BODY — BRASS, NICKEL PLATING	RELEASE TO MFG
CONTACT — BRASS, SILVER PLATING INSULATOR — PTFE 2. ELECTRICAL: A. IMPEDANCE: 50 OHM B. FREQUENCY RANGE: DC 0-4 GHz C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN. 3. MECHANICAL: A. DURABILITY: 500 CYCLES MIN. B. TEMPERATURE RANGE: — 65°C to +165°C	P REDRAWN AND UPDATED DWGS, ADD COD 4/11/12 48988 CPM
Ø.573 REF Ø.500 REF	.474 REF Ø.090 REF .100 REF .100 REF
STAMP "74868 UG-932 A/U"	.437 HEX 7/16 WRENCH FLATS
±.010 ±.010 .100	Ø.257 REF
RECOMMENDED CABLE STRIPPING DIMENSIONS	CUSTOMER OUTLINE DRAWING ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY
1.000 (0,127MM)	McGRATH 3/20/12 MHV UG 932 A/U CONNECTOR Daphury CT USA Tainan Taiwan Shenzhen China
	NEER DATE CAPOZZI PLUG (FOR RG-59/U, www.amphenolrf.com
are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensina, aranting	62/U & 71/U CABLES.) DRAWING NO. 27975 SCALE: 3/1 SHEET 2 OF 2 ITEM NO. 27975
NOTICE — These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	DWG SIZE CODE ID REV PART NO. 27975 B 74868 P 27975