






LOC		DIST	P		ZONE	LTR	REVISIONS		
GP	00						DESCRIPTION	DATE	APPD
						G	REVISED PER EC 0513-0018-03	28AUG03	JG



1. DIMENSION EQUALS .568 WHEN FULLY TERMINATED.
2. .000030 MIN. GOLD ON GOLD PLATE AREA, .000100 MIN. BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL.
3. ASSEMBLY DESIGNED FOR #26 AND #28 AWG STRANDED CONDUCTOR AND #26, #28 AND #30 AWG SOLID CONDUCTOR RIBBON CABLE ON .050 CENTERS.
4. .000030 MIN. GOLD ON GOLD PLATE AREA, .000100 MIN. BRIGHT TIN ON TERMINATION END, ALL OVER .000050 NICKEL.



DETAIL Z
SCALE 10:1

	4		CONTACTS LOADED IN ROWS A & C	746603-4
OBSOLETE		2	CONTACTS LOADED IN ROWS B & C	746603-3
OBSOLETE	2		CONTACTS LOADED IN ROWS A & B	746603-2
		2	CONTACTS LOADED IN ROWS A & C	746603-1

CONTACT FINISH		DESCRIPTION		PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± .005 3 PLC DEC ± .005 ANGLES ± 1° MATERIAL HOUSING & COVER GLASS FILLED POLYESTER 94 V-0 RATED COLOR:BLACK CONTACTS: PHOSPHOR BRONZE FINISH CONTACTS: SEE TABLE		DR 11-1-89 D KEITZER		 AMP INCORPORATED Harrisburg, Pa. 17105 NAME ASSEMBLY, EUROLATCH AMP-LATCH	
		CHK -			
		APPD -			
		APPD -			
		PRODUCT SPEC 108-46003			
APPLICATION SPEC -		SIZE D	CAGE CODE 00779	DRAWING NO 746603	
WEIGHT -		SCALE 4:1	SHEET 1 OF 1		