





PREBENT MOUNTING EAR
(WHEN SPECIFIED)



CIRCUIT NUMBER
IDENTIFICATION RIBS








PLUG

3	E2	
2	D	
1	E4	
<input checked="" type="checkbox"/>	SH.	REV. LTR. REVISIONS

DIMENSIONS SHOWN METRIC (INCH)		▽ = 0	▼ = 0	REVISE ONLY ON CAD SYSTEM	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± .001 TO		TITLE .093/(2.36) HOUSING, PLUG AND RECEPTACLE, 2 CKT ± .264/(6.70) CTRS.			
INCH METRIC		PART NO.		DRAWG. NO.	
3 PLACE ± .010	---	L15LEJLL.		60532	
2 PLACE ± .014	± 0.25	MOLEX INCORPORATED		SHEET NO. DATE	
1 PLACE ---	± 0.35	U.S.A.		1 of 3 11/21/88	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-3191-2*	
DRWG. BY: CEP	CHKD. BY: RW	FILE NAME: S31912X1	DRWG. NO.:	REV.:	SIZE:
APP'D. BY: RAS	SCALE: 2 : 1	DATE:			CP C

E4	REVISED UCR 98-0148 WANG 98-04-15
E3	ADD RAMP DIM'S ECN #U4 0293 3-1-94 RW
E2	X-REMOVE ECR U3 0001 GC 12/30/92 RW
E1	REL. RED VERSIONS ECR U1 2167 GC 1/24/92 RW
E	REV. MATL. CODE ECR # U90901 KBW 01-25-89 RW
D	REV. & REDRAWN ECR UB 1858 GEP 11-21-88 RW

NO P.S. 1



RECEPTACLE



DIMENSIONS SHOWN METRIC (INCH)		REVISIONS	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± .005° TO		D	
INCH METRIC		SEE SHT. 1	
3 PLACE ± .010	---	LTR.	REVISIONS
2 PLACE ± .014	± 0.25	LTR.	REVISIONS
1 PLACE ---	± 0.35	LTR.	REVISIONS
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		LTR.	
DRAWN: GEP		DATE: 11/21/88	
BY: RAS		SCALE: 2:1	
CHECKED: RW		PART NO. SD-3191-2*	
SCALE: 2:1		DRWG. NO. SD-3191-2*	
FILE NAME: 531912X2		DIV. CP	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE	

PLUG		RECEPTACLE	
PART NO.	ENG. NO.	PART NO.	ENG. NO.
19-09-2028	3191-2P	19-09-1029	3191-2R1
19-09-2029	3191-2P1	19-09-1026	3191-2R1-201
19-09-2027	3191-2P-201	19-09-1020	3191-2R IRD
19-09-2026	3191-2P1-201	19-09-1021	3191-2R1BU
19-09-2020	3191-2P IRD		
19-09-2021	3191-2P1BU		

LEGEND:

3191-2*****
 CIRCUIT SIZE
 P = PLUG
 R = RECEPTACLE
 EARS: BLANK = WITH PREBENT EARS (PLUG ONLY)
 I = WITHOUT EARS

COLOR: BLANK = NATURAL COLOR
 AM=AMBER BK=BLACK BU=BLUE
 BN=BROWN GY=GRAY GN=GREEN
 OR=ORANGE RD=RED YW=YELLOW
 MATERIAL: BLANK=NYLON TYPE 6/6, 94V-2
 201=NYLON TYPE 6/6, 94V-0



NOTES:

1. THESE HOUSINGS FOR USE WITH MOLEX .093/(2.36) DIAMETER SERIES TERMINALS.

DIMENSIONS SHOWN (METRIC) INCH		▽ = 0 ▼ = 0		REVISE ONLY ON CAD SYSTEM	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± .04° 1°		TITLE		.093/(2.36) HOUSINGS PLUG AND RECEPTACLE 2 CKT ±.264/(6.70) CTRS.	
INCH METRIC		PART NO.		SHEET NO. DATE	
3 PLACE ± .010	---	MOLEX INCORPORATED		3 11/21/88	
2 PLACE ± .014	± 0.25	L15LEJLL 60532 U.S.A.		DRWG. NO.	
1 PLACE ---	± 0.35	SEE CHART		SD-3191-2*	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		FILE NAME		DIV. SIZE	
DRWG. BY CEP		531912X3		CP C	
APP'D. BY RAS		SCALE ---:--		NO P.S. 1	

LTR.	REVISIONS	LTR.	REVISIONS
E2	SEE SHEET I		
E1	SEE SHEET I		
E	SEE SHEET I		
D	SEE SHEET I		