







LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
B		REVISED (ECR-11-003466)		17FEB11	SC	WK	



- NOTES:  
 1. MATERIAL:  
 1.1 HOUSING/BACK COVER: THERMOPLASTIC(PBT), UL94V-0; COLOR: SEE TABLE.  
 1.2 CONTACTS: COPPER ALLOY  
 1.3 BOARDLOCK: COPPER ALLOY  
 1.4 BRACKET: ZINC ALLOY  
 1.5 SHELL: STEEL  
 2. FINISH:  
 2.1 CONTACT: GOLD PLATING (SEE TABLE) ON CONTACT AREA. 2.54µm[100µ"] MIN. MATTE TIN PLATING ON SOLDER TAIL AREA, 1.27µm[50µ"] MIN. NICKEL UNDERPLATING OVERALL.  
 2.2 BOARDLOCK: 1.52µm[60µ"] MIN. MATTE TIN PLATING OVERALL, 1.27µm[50µ"] MIN. NICKEL UNDERPLATING OVERALL.  
 2.3 SHELL: 1.52µm[60µ"] MIN. BRIGHT TIN PLATING OVERALL.  
 3. WAVE SOLDER CAPABLE TO 265°C PER TE SPEC. 109-202, CONDITION B.



X-1734280-6	30 u"	PC99/ACTUAL COLOR	37-37 NOT AVAILABLE
X-1734280-5	10 u"	PC99/ACTUAL COLOR	
X-1734280-4	GOLD FLASH	PC99/ACTUAL COLOR	
X-1734280-3	30 u"	BLACK	
X-1734280-2	10 u"	BLACK	
X-1734280-1	GOLD FLASH	BLACK	
PART NO.	GOLD PLATING	HSG COLOR	

3-1734280-X	37-37	69.34	63.50	55.42	49.86
2-1734280-X	25-25	53.10	47.04	38.96	33.24
1-1734280-X	15-15	39.30	33.30	25.25	19.39
1734280-X	9-9	30.95	24.99	16.92	11.08
PART NO.	PINS	A	B	C	D

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 0.5 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.15 4 PLC ± - ANGLES ± 3°	DWN S. CHIEN 18MAY2009 CHK S. CHIEN 18MAY2009 APVD W. KODAMA 18MAY2009	Tyco Electronics Corporation Taipei, Taiwan	
MATERIAL: SEE NOTE	FINISH: SEE NOTE	PRODUCT SPEC: 108-57517 APPLICATION SPEC: 501-57590 WEIGHT: - GRAMS	NAME: D-SUB STACKED PLUG OVER PLUG, R/A TYPE, WITH #4-40 SCREWLOCK. SIZE: A3 CAGE CODE: 00779 C=1734280 DRAWING NO: 1734280 RESTRICTED TO: -	
CUSTOMER DRAWING		SCALE: -	SHEET: 1 OF 2	REV: B

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG., 2006.

© COPYRIGHT 2009 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

NOTES:

1. DIMENSION:



TRAY: L=310, W=215, H=30

CARTON: L=335, W=230, H=280


2. TRAY: PS or PET

3. QUANTITY:


PIN NO.	9-9	15-15	25-25	37-37
PCS/TRAY	36	28	20	16
TRAY/CARTON	10	10	10	10
PCS/CARTON	360	280	200	160
NET WT.(KG)	10.27	9.95	9.5	10.6
GROSS WT.(KG)	11.72	11.30	10.93	11.7



TOP COVER




TRAY



CARTON

LABEL



LABEL

TRAY LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan	
DIMENSIONS: MM		CHK	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D-SUB STACKED PLUG OVER PLUG, R/A TYPE, WITH #4-40 SCREWLOCK.	
0 PLC ± -		PRODUCT SPEC	SIZE	CAGE CODE
1 PLC ± -		APPLICATION SPEC	A3	00779
2 PLC ± -		WEIGHT	DRAWING NO	
3 PLC ± -		CUSTOMER DRAWING	C=1734280	
4 PLC ± -		SCALE	SHEET	REV
ANGLES ± -		2 OF 2	B	