THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION - , - . EC LOC DIST REVISIONS ALL RIGHTS RESERVED. (C) COPYRIGHT -DESCRIPTION RK HMF REVISED PER ECO-11-005150 19MAR11 ITEMS PROVIDED TO THIS SPECIFICATION TO BE PERMANENTLY IDENTIFIED PER THE FOLLOWING IDENTIFIER: YEAR - WEEK TE CONNECTIVITY PART NUMBER DATE CODE (e.g. 0625) XXXXXXX-X'XXXX 4. ALL DIMENSIONS SHOWN ACROSS A CENTERLINE (\$\mathbb{L}\$) SHALL BE CENTRALIZED WITHIN THE TOLERANCE INDICATED FOR THAT DIMENSION. 3. FINISHES: CROWN HOLDER: GOLD PLATED, .000030 MIN THICK WITH OVERALL GOLD FLASH OVER NICKEL PLATED, .000040 MIN THICK 2. MATERIALS: INSULATOR: THERMOPLASTIC, GLASS REINFORCED, UL94V-0 FLAMMABILITY RATED, COLOR-BLACK CROWN HOLDER: COPPER ALLOY 1643906-1 AS SHOWN CROWN BAND: COPPER ALLOY MATING BLADE: COPPER ALLOY WITH GOLD OR NICKEL PLATED PART NUMBER DESCRIPTION 1. PART NUMBER CHANGES AND DR DESIGN CHANGES AFFECTING 02/25/06 THIS DRAWING IS A CONTROLLED DOCUMENT. ITEM INTERCHANGEABILITY REQUIRE PRIOR ELCON APPROVAL TE Connectivity AND AUTHORIZATION BY REVISION TO THIS DRAWING. STEVE FLICKINGER
RODUCT SPEC TOLERANCES UNLESS OTHERWISE SPECIFIED: DIMENSIONS: NOTES: UNLESS OTHERWISE SPECIFIED INCH(MM) CONNECTOR, CROWN CLIP SINGLE POLE APPLICATION $\pm 0.02(0.3)$ APPLICATION SPEC $\pm 0.10(0.25)$ SIZE CAGE CODE DRAWING NO RESTRICTED TO MATERIAL A3|00779|**C-**1643906| FINISH WEIGHT CUSTOMER DRAWING 2.1 1 OF 2 1470-19 (3/11)

