


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-09-002275	30/03/09	AM	JS

- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - UL NUMBER E13288
 - MATERIAL: BODY - COPPER
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838144-0	0.5mmsq-1.5mmsq 22-16 (AWG)	4.0mm STUD SIZE STANDARD ENTRY	RED RING TERMINAL (INSULATED)	3000	1000	4.30	6.60	20.40	4.30	10.50	0.75	0.80	0.5mmsq-1.5mmsq 22-16(AWG)	4.0	RED RING TERMINAL (INSULATED)	2-1838144-0			
1-1838144-0				3500	100											1-1838144-0			
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	d2 (±0.20)	B (±0.30)	L (±1.50)	D (±0.50)	E (±1.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	STUD SIZE (mm)	DESCRIPTION	PART No			
						DIMENSIONS													
										THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Raghunandan 18JUL05		Tyco Electronics Corporation Bideford, UK, EX39 4HE					
										CHK S. Parlow 03/04/07		NAME							
										APVD F. Wheeler-King 03/04/07		PRODUCT SPEC		EURO-CRIMP INSULATED RED RING TERMINAL 0.5mmsq-1.5mmsq / 22-16 AWG RANGE					
										APPLICATION SPEC		—							
										MATERIAL		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
										—		—		A2	00779	C=1838144	—		
										FINISH		CUSTOMER DRAWING		SCALE	NTS	SHEET	1 OF 2	REV	B



BOX NOTES:

- | | |
|---|--|
| 1.  EURO SLOT: | TO BE POSITIONED TO CENTRE ON FRONT COVER. |
| 2.  BOX HINGE: | FRONT COVER TO BE HINGED ON RIGHT SIDE. |
| 3. SPECIFICATION: | COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES. |
| 4. LABEL: | CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE. |

PACK SPECIFICATION:

- | | |
|------------------------|--|
| 1. CLEAR PLASTIC BOX: | PART NUMBER 1--0 TO BE PACKED 100 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX. |
| 2. CLEAR PLASTIC BAG: | PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR A 1000 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 3 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX. |
| 3. INNER CARTON LABEL: | LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 3000 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED. |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Raghunandan 18JUL05		 Tyco Electronics Corporation Bideford, UK, EX39 4HE		
		CHK S. Parlow 03/04/07				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME EURO-CRIMP INSULATED RED RING TERMINAL 0.5mmsq-1.5mmsq / 22-16 AWG RANGE		
		APVD F. Wheeler-King 03/04/07				
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		SIZE A2				CAGE CODE 00779
MATERIAL —		FINISH —		WEIGHT —		
		CUSTOMER DRAWING		SCALE NTS	SHEET 2 OF 2	REV B