






REVISONS		DATE	DWN	APVD
AD	00			
B	REV PER ECO-11-007577	13APR2011	RKC	JE



- 1 REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
 - 2 MATERIAL:
SHIELD - PHOSPHOR BRONZE
CONTACT - COPPER-NICKEL-SILICON
HOUSING, CHICKLET AND CHICKLET COVER - GLASS FILLED POLYESTER, UL 94V-0 RATED.
 - 3 FINISH: SIGNAL AND GROUND CONTACTS:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING
 - 4 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN
 - 5 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
 - 6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.

RECOMMENDED PC BOARD LAYOUT, DAUGHTER BOARD, COMPONENT SIDE SHOWN
 SCALE 4:1



6469001-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: S. J. MAGARO 26APR2004	TE Connectivity
DIMENSIONS: mm		CHK: R. A. PATTERSON 26APR2004	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: R. A. PATTERSON 26APR2004	NAME: RECEPTACLE ASSEMBLY, 4 PAIR, HMZd
9 PLC	±	PRODUCT SPEC	SIZE: CAGE CODE: DRAWING NO: A100779C=6469001
3 PLC	±	APPLICATION SPEC	RESTRICTED TO
4 PLC	±	WEIGHT	SCALE: 8:1 SHEET 1 OF 1 REV B
4 PLC	±	CUSTOMER DRAWING	