

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

MATERIAL:

HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.

TERIMINAL: BRIGHT TIN PLATED, COPPER ALLOY.

SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.

ELECTRICAL:

UL CLASS C: 20A, 150V.

UL CLASS D: 10A, 300V.

CSA TYPE B: 20A, 300V.

CSA TYPE C: 20A, 300V.

CSA TYPE D: 10A, 300V.

CSA TYPE E: 20A, 300V.

WIRE RANGE: 12-22 AWG

MECHANICAL:

MAXIMUM TORQUE RATING: 7 IN-LBS.

RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS

OTHERWISE STATED.

1 SCREWS ARE BOTTOMED, NO THREAD INTERRUPT.





2 SCREWS ARE NICKEL PLATED BRASS.

3 SCREWS ARE CAPTIVE.

4 SEE FIGURE.

5 PRELIMINARY PART NUMBER.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PCB LAYOUT

LOC FT	DIST 0	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			N4	REVISED PER ECO-12-015450	27AUG12	KH	ME
.160		4DB-P108-16-105	5.590	17	2-796628-4		
.160		4DB-P108-17	5.590	17	4-1437667-2		
.160		4DB-P108-16	5.265	16	4-1437667-0		
.160		4DB-P108-15	4.940	15	3-1437667-9		
.160		4DB-P108-14-102	4.615	14	2-796658-5		
.160		4DB-P108-14-102	4.615	14	2-796658-3		
.160		4DB-P108-14	4.615	14	3-1437667-8		
.160		4DB-P108-13	4.290	13	3-1437667-7		
.160		4DB-P108-12	3.965	12	3-1437667-6		
.160		4DB-P108-11	3.640	11	3-1437667-5		
.160		4DB-P108-10	3.315	10	3-1437667-3		
.160		4DB-P106-09-094	2.990	9	1-796658-7		
.160		4DB-P108-09	2.990	9	3-1437667-2		
.160		4DB-P108-08-091	2.665	8	1-796658-4		
.160		4DB-P108-08	2.665	8	3-1437667-1		
.160		4DB-P106-07-100	2.340	7	2-796658-2		
.160		4DB-P106-07-093	2.340	7	1-796658-6		
.160		4DB-P108-07	2.340	7	3-1437667-0		
.160		4DB-P106-06-099	2.015	6	2-796658-1		
.160		4DB-P108-06-090	2.015	6	1-796658-3		
.200		4DB-P108-06	2.015	6	2-796658-6		
.160		4DB-P108-06	2.015	6	2-1437667-9		
.160		4DB-P106-05-098	1.690	5	2-796658-0		
.160		4DB-P108-05-093	1.690	5	1-796658-5		
.160		4DB-P108-05	1.690	5	2-1437667-8		
.160		4DB-P106-04-097	1.365	4	1-796658-9		
.160		4DB-P108-04-089	1.365	4	1-796658-2		
.160		4DB-P108-04	1.365	4	2-1437667-6		
.160		4DB-P106-03-096	1.040	3	1-796658-8		
.160		4DB-P108-03-088	1.040	3	1-796658-1		
.160		4DB-P108-03	1.040	3	2-1437667-5		
.142		4DB-P108-02-142	.715	2	2-796658-7		
.160		4DB-P108-02	.715	2	2-1437667-4		
DIM B	CATALOG NUMBER		DIM A	NO OF POSN	PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S WELDON 01MAY2003

CHK S YODER 5/1/03

APVD S YODER 5/1/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE TE Connectivity

NAME

ASSEMBLY, DUAL BARRIER
4DB-P108-XX

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2-1437667-4


SCALE NTS

SHEET

1 OF 2

REV N4

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION			DATE	APVD
		SEE SHEET 1			-	-



2-796658-4

.160	4DB-P108-30	9.815	30	5-1437667-5
.160	4DB-P108-29	9.490	29	796658-9
.160	4DB-P108-28	9.165	28	5-1437667-3
.160	4DB-P108-27	8.840	27	796658-8
.160	4DB-P108-26	8.515	26	5-1437667-2
.160	4DB-P108-25	8.190	25	796658-7
.160	4DB-P108-24	7.865	24	5-1437667-0
.160	4DB-P108-23	7.540	23	796658-6
.160	4DB-P108-22	7.215	22	4-1437667-8
.160	4DB-P108-21	6.890	21	796658-2
.160	4DB-P108-20	6.565	20	4-1437667-6
.160	4DB-P108-19	6.240	19	4-1437667-5
.160	4DB-P108-18	5.915	18	4-1437667-4
DIM B	CATALOG NUMBER	DIM A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .01
3 PLC ± .005
4 PLC ± -
ANGLES ± 1°
FINISH
-

DWN S WELDON 01MAY2003
CHK S YODER 5/1/03
APVD S YODER 5/1/03
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

TE Connectivity

NAME
ASSEMBLY, DUAL BARRIER
4DB- P108-XX
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2-1437667-4

RESTRICTED TO
-

CUSTOMER DRAWINGSCALE NTS
SHEET 2 OF 2
REV N4

1470-19 (3/11)