


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		B	ECR-09-002275	30/03/09	AM	JS

- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - UL NUMBER E13288
 - MATERIAL: BODY - COPPER
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838154-0	1.5mmsq-2.5mmsq 16-14 (AWG)	6mm STUD SIZE STANDARD ENTRY	BLUE RING TERMINAL (INSULATED)	2000	1000	6.40	12.00	28.10	4.70	11.00	0.80	0.80	1.5mmsq-2.5mmsq 16-14(AWG)	6.0	BLUE RING TERMINAL (INSULATED)	2-1838154-0	
1-1838154-0				3500	100											1-1838154-0	
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	d2 (±0.20)	B (±0.30)	L (±1.50)	D (±0.50)	E (±1.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	STUD SIZE (mm)	DESCRIPTION	PART No	
						DIMENSIONS											
										THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Raghunandan 19JUL05		Tyco Electronics Corporation Bideford, UK, EX39 4HE			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK S. Parlow 04/04/07		APVD F. Wheeler-King 04/04/07		NAME									
		0 PLC ± 0.5		APVD		PRODUCT SPEC		EURO-CRIMP INSULATED BLUE RING TERMINAL 1.5mmsq-2.5mmsq / 16-14 AWG RANGE									
		1 PLC ± 0.2		—													
		2 PLC ± 0.1		APPLICATION SPEC		—		SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO				
		3 PLC ± 0.015		—		—		A2		00779	C=1838154		—				
MATERIAL		FINISH		WEIGHT		—		SCALE		NTS	SHEET		1	OF	2	REV	B
—		—		—		—		CUSTOMER DRAWING									



- LABEL NOTES:

1. PERFORATED LINE:

DOTTED LINE TO BE ALIGNED WITH OPENING EDGE & FOLDED TO LEFT SIDE OF BOX.

2. LOGO:

USE LATEST REVISION OF TYCO COMPANY LOGO.

3. LINE1:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 1.

4. PART NUMBER:

FOR 1--0 & 2--0 USE TYCO PART NUMBER.
1--0 = 1-1838154-0
2--0 = 2-1838154-0

5. LINE 2:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 2.

6. LINE 3:

SEE SHEET 1, USE TEXT FROM COLUMN PACKAGING LABEL DESCRIPTION LINE 3.

7. QTY:

SEE SHEET 1, USE NUMBER FROM THE COLUMN QTY.

8. EAN BARCODE.

USE LATEST TYCO BARCODE SUPPLIED.
1--0 = TYCO BARCODE
2--0 = TYCO BARCODE

9. UL:

WHERE APPLICABLE USE UL LOGO, SEE SHEET 1.

10. PRODUCT PICTURE:

A PRODUCT PICTURE IS REQUIRED.
- BOX NOTES:

1. EURO SLOT:

TO BE POSITIONED TO CENTRE ON FRONT COVER.

2. BOX HINGE:

FRONT COVER TO BE HINGED ON RIGHT SIDE.

3. SPECIFICATION:

COVER TO BE FREE FROM POSSIBLE WARPING & CAPABLE OF BEING RE-SEALED MIN 100 TIMES.

4. LABEL:

CORRECT CUSTOMER BOX LABEL TO BE POSITIONED ON THE FRONT COVER WITH THE PERFORATED EDGE ON THE LEFT HAND SIDE.
- PACK SPECIFICATION:

1. CLEAR PLASTIC BOX:

PART NUMBER 1--0 TO BE PACKED 100 PARTS PER CLEAR PLASTIC BOX (FIG2) WITH THE CORRECT CUSTOMER LABEL (FIG1), 35 CLEAR PLASTIC BOXES OF THE SAME PART NUMBER ARE TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

2. CLEAR PLASTIC BAG:

PART NUMBER 2--0, USE A SUITABLE CLEAR PLASTIC BAG FOR A 1000 PARTS, POSITION AN APPROPRIATE LABEL AS IN FIG1 BUT WITHOUT THE PERFORATED SIDE, CENTRE OF BAG. 2 BAGS ARE THEN TO BE PACKED INTO A SUITABLE INNER CARTON BOX.

3. INNER CARTON LABEL:

LABEL AS PER CLEAR PLASTIC BAG NOTE 2 BUT WITH INNER CARTON QTY 2000 TO BE POSITIONED ON THE SIDE OF THE BOX FOR VIEWING WHEN STORED.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

19JUL05

K.Raghu

CHK

04/04/07

S. Parlow

APVD

04/04/07

F. Wheeler-King

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Bideford, UK, EX39 4HE

NAME

EURO-CRIMP INSULATED BLUE RING TERMINAL

1.5mmsq-2.5mmsq / 16-14 AWG RANGE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=1838154

—

SCALE

NTS

SHEET

2

OF

2

REV

B

AMP 1471-9 REV 31MAR2000