






| LOC | DIST | REVISIONS |         |                   |         |     |
|-----|------|-----------|---------|-------------------|---------|-----|
| FT  | 64   | REV       | LTR     | DESCRIPTION       | DATE    | DWN |
|     |      | L1        | REVISED | PER ECO-11-005027 | 11MAR11 | RK  |



SECTION A-A  
ROTATED 90° CW  
SCALE 10:1  
FOR -6,-7 & -8 ONLY



SECTION A-A  
ROTATED 90° CW  
SCALE 10:1  
FOR -1,-2 & -3 ONLY



|                   |                |               |                                          |            |
|-------------------|----------------|---------------|------------------------------------------|------------|
| OBSOLETE          | TINNED         | PHOS.BRZ.     | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 2-643644-3 |
|                   | TINNED         | PHOS.BRZ.     | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-8   |
| OBSOLETE          | TINNED         | BE.CU.        | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-7   |
| SUPSD BY 643644-2 | TINNED         | BE.CU.        | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-6   |
|                   | TINNED         | PHOS.BRZ.     | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-4   |
| OBSOLETE          | TINNED         | PHOS.BRZ.     | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-3   |
|                   | TINNED         | BE.CU.        | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-2   |
|                   | TINNED         | BE.CU.        | GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK | 643644-1   |
|                   | CONTACT FINISH | CONTACT MAT'L | HOUSING MATERIAL                         | PART NO.   |

|                                                                                       |                                           |                            |                                                                                                       |                                                |            |               |     |    |
|---------------------------------------------------------------------------------------|-------------------------------------------|----------------------------|-------------------------------------------------------------------------------------------------------|------------------------------------------------|------------|---------------|-----|----|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                           | DWN<br>M. CYRUS<br>7-3-84  |  TE Connectivity |                                                |            |               |     |    |
|                                                                                       |                                           | CHK<br>N. JONES<br>7-3-84  |                                                                                                       |                                                |            |               |     |    |
| DIMENSIONS:<br>INCHES                                                                 | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: | APVD<br>J. GRAY<br>7-10-84 | NAME                                                                                                  | SOCKET ARVD, SIP, 12 POS,<br>DIPLOMATE DL<br>— |            |               |     |    |
|                                                                                       |                                           | PRODUCT SPEC               |                                                                                                       |                                                |            |               |     |    |
|  | 0 P/LC ± —                                | APPLICATION SPEC           | SIZE                                                                                                  | CAGE CODE                                      | DRAWING NO | RESTRICTED TO |     |    |
|                                                                                       | 2 P/LC ± —                                |                            |                                                                                                       |                                                |            |               |     |    |
|                                                                                       | 3 P/LC ± —                                | 114-1049                   | A1                                                                                                    | 00779                                          | C=643644   | —             |     |    |
|                                                                                       | 4 P/LC ± —                                |                            |                                                                                                       |                                                |            |               |     |    |
| MATERIAL                                                                              | FINISH                                    | WEIGHT                     |                                                                                                       |                                                |            |               |     |    |
| SEE TABLE                                                                             | SEE TABLE                                 | —                          | CUSTOMER DRAWING                                                                                      |                                                |            |               |     |    |
|                                                                                       |                                           |                            | SCALE                                                                                                 | 5:1                                            | SHEET      | 1 OF 1        | REV | L1 |