

DRAWING MADE IN THIRD ANGLE PROJECTION


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT BY




LOC
AA DIST
22

REVISIONS

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
		F4		REVISED PER ECO-11-005033	2APR11	RK HMR



1. BARREL TERMINAL WIRE RANGE: 19-28 AWG SOLID OR STRANDED WIRE MAX INSULATION DIA IS .065.
2. MOUNTING PANEL THICKNESS: .062 NOMINAL.
3. MATERIAL: 6 POSITION STUFFER CAP - POLYCARBONATE, NATURAL. DISCRETE STUFFER CAP - NYLON 6/6. BARREL TERMINAL - TIN COATED PHOSPHOR BRONZE. CONTACTS - NICKEL PLATED HIGH STRENGTH COPPER ALLOY HAVING SELECTIVE GOLD PLATING ON CONTACT AREA AND SELECTIVE TIN PLATING ON BARREL TERMINAL AREA. HOUSING AND KEYSTONE - THERMOPLASTIC, 94 V-0 RATED, SEE TABLE.
4. STUFFER CAPS SHIPPED NOT ASSEMBLED.
5. BARREL TERMINALS WILL ACCOMMODATE ONE OR TWO WIRES OF THE SAME TYPE AND WITHIN PLUS OR MINUS ONE WIRE GAUGE SIZE.

INNER PANEL CUTOUT
SCALE 2:1FRONT PANEL CUTOUT
SCALE - 2:1

WIRING DIAGRAM

OBSOLETE	LT ALMOND	NATURAL	22-26 AWG	KIT WITH 1 SIX POSITION STUFFER CAP	5-554171-4
	BLACK	YELLOW	19-22 AWG	KIT WITH SIX DISCRETE STUFFER CAPS	5-554171-3
		NATURAL	24-28 AWG		5-554171-2
			22-26 AWG	KIT WITH 1 SIX POSITION STUFFER CAP	5-554171-1
OBSOLETE	LT ALMOND	NATURAL	22-26 AWG	KIT WITH 1 SIX POSITION STUFFER CAP	-4
		YELLOW	19-22 AWG	KIT WITH 6 DISCRETE STUFFER CAPS	3
OBSOLETE	BLACK		24-28 AWG		2
		NATURAL	22-26 AWG	KIT WITH 1 SIX POSITION STUFFER CAP	554171-1
HOUSING COLOR		STUFFER CAP COLOR	WIRE RANGE	DESCRIPTION	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.			CONTRACT NO	TE Connectivity	
TOLERANCES ON:			DR C. Yates 6-20-85		
DECIMALS ± .010			CHK Stephen D. 7-1-85		
ANGLES ±			Gene Reed 7-01-85		
MATERIAL			APPD B. W. Johnson 7-1-85	NAME KEYSTONE JACK KIT, 6 POSITION, COMMERCIAL	
FINISH			APPD		
			DSGN APPD	SIZE C	FSCM NO 00779
			OTHER APPD	DRAWING NO 554171	REV F4
				SCALE 4:1	SHEET 1 OF 1

CUSTOMER DRAWING