

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC GP DIST 00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER ECO-11-005033	23MAR11	RK	HMR



1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY STANDARD 230-702.

2. HIROSE COMPATIBLE, 2.5 mm MATING HEIGHT. UMCC CONNECTOR TYPE III.

3. CABLE ASSEMBLY TO BE 100% ELECTRICALLY TESTED FOR OPENS, SHORTS AND CONTINUITY. HI-POT AT 150 VDC FOR 100mS VSWR: 1.5:1 MAX.



2032439-1

PART NO.

QTY	PC	DESCRIPTION	ITEM
1	PC	TUBING, HEAT SHRINK	3
1	PC	SMA, PLUG	2
1	PC	UMCC, PLUG WITH 1.37 CABLE	1
-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 04/DEC/07 E.C. CLAYBAUGH	TE Connectivity CABLE ASSY, RF, UMCC PLUG TO SMA PLUG [1.37mm CABLE]		
DIMENSIONS: mm [INCHES]		CHK 04/DEC/07 J. ORNER			NAME
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 04/DEC/07 J. ORNER			SIZE
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC			CAGE CODE
MATERIAL		FINISH	APPLICATION SPEC	DRAWING NO	
-		-	WEIGHT	RESTRICTED TO	
			-	A300779	
			CUSTOMER DRAWING	G-2032439	
			SCALE	SHEET	
			N.T.S.	1 OF 1	
				REV A1	