





- 1 WIRE RANGE: 0.2–0.82mm² (24–18 AWG).
- 2 INSULATION RANGE: 1.50 – 3.10 DIA.
- 3 FINISH: 0.76µm MIN GOLD OVER 1.27µm MIN NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 4 FINISH: 2.54µm MIN PRE-TIN ON ALL SURFACES IN THIS AREA.
- 5 FINISH: 2.54µm MINIMUM PRE-TIN ALL OVER.



GOLD	34	PHOS. BRZ.	794956-4
PRE-TIN	5	PHOS. BRZ.	794956-3
GOLD	34	BRASS	794956-2
PRE-TIN	5	BRASS	794956-1
FINISH:		MATERIAL:	PART NO.

1471-9 (3/11)

SECTION A-A

SECTION B-B

SECTION C-C

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ± 0.15 [.006]
2 PLC ± 0.10 [.004]
3 PLC ± 0.050 [.0020]
4 PLC ±
ANGLES ±
FINISH

DWN
S. HAMM
10-SEP-2001

CHK
D. COLEY
10-SEP-2001

APVD
D. COLEY
10-SEP-2001

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=794956

RESTRICTED TO
-

SCALE
NTS

SHEET
1 of 1

REV
H3