








Customer Information Sheet


DRAWING No.: S1761-XXR SHEET 2 OF 2 IF IN DOUBT - ASK © NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm




REEL DETAILS



- NOTES:
- 1. QUANTITY PER REEL = 2000
 - 2. THIS PRODUCT IS TAPED AND REELED IN ACCORDANCE WITH EIA-481 (ELECTRONIC INDUSTRIES ASSOCIATION)



REELING DIRECTION



SINGLE COMPONENT DIMENSIONS

ORDER CODE: **S1761-XXR**

FINISH _____

42 = GOLD FLASH ON CONTACT AREA,
2.5µ 100% TIN ON FOOT AREA,
0.76-1.27µ ALL OVER NICKEL

46 = 0.76-1.27µ 100% TIN OVER NICKEL

COMPONENT SPECIFICATION:

MATERIAL = TITANIUM COPPER

RECOMMENDED WORKING HEIGHT = 2.50mm / MIN FORCE = 1.5N

MINIMUM WORKING HEIGHT = 1.75mm / MAX FORCE = 8.5N

MAXIMUM PERMANENT SET = 0.20mm

HARWIN			THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.	TOLERANCES X. = $\pm 1\text{mm}$ X.X = $\pm 0.25\text{mm}$ X.XX = $\pm 0.10\text{mm}$ X.XXX = $\pm 0.01\text{mm}$ ANGLES = $\pm 5^\circ$ UNLESS STATED	MATERIAL: SEE ABOVE		TITLE: S1761-XX EMI SHIELD FINGER IN TAPE AND REEL			
HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com		HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk			HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg		DRAWING NUMBER: S1761-XXR		SHT 2 OF 2	
					FINISH: SEE ABOVE					
						S/AREA: mm ²				

SM	5	08.06.10	10822
NAME	ISS.	DATE	C/NOTE
APPROVED: S. MCCULLAGH			
CHECKED: R. ADDE			
DRAWN: N. CODLING			
CUSTOMER REF.:			
ASSEMBLY DRG:			