


1. MATES WITH HOUSING 350735.
2. NOTE DELETED.
3. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
4. CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND TIN LEAD ON SOLDER TAIL END.
5. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
6. CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
7. DIMENSIONS IN BRACKETS ARE IN INCHES.

PHOSPOR BRONZE, GOLD	NYLON, UL94V-0, NATURAL	350713-4
PHOSPOR BRONZE, GOLD	NYLON, UL94V-0, NATURAL	350713-2
PHOSPOR BRONZE, PRE-TIN	NYLON, UL94V-0, NATURAL	350713-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL AND COLOR	PART NUMBER

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN K. WHITAKER 25 JULY 2005	NAME	
DIMENSIONS: mm (INCHES)		CHK S. RIDGILL 25 JULY 2005	STE TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. RIDGILL 25 JULY 2005	PIN HEADER ASSEMBLY, 12 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
		PRODUCT SPEC	SIZE	
9 PLC ±		-	CAGE CODE	
3 PLC ±		-	DRAWING NO	
5 PLC ±		-	RESTRICTED TO	
4 PLC ±		-	A100779	
ANGLES ±		-	C=350713	
FINISH		WEIGHT	-	
SEE TABLE		CUSTOMER DRAWING		SCALE
				1:1
				SHEET
				OF
				REV
				M