




LOC		DIST		REVISIONS			
AD	00	REV	DATE	BY	CHK	APPD	
A		REV PER ECO-11-007577	13APR2011	RKC		JE	




RECOMMENDED PC BOARD LAYOUT
 COMPONENT SIDE SHOWN
 SCALE 4:1

- 1 REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- 2 MATERIAL:
 CONTACT & SHIELD - PHOSPHOR BRONZE
 HOUSING & CHICKLET - GLASS FILLED POLYESTER
- 3 FINISH: SIGNAL AND GROUND CONTACTS:
 MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
 COMPLIANT PIN AREA: 0.5 μm MIN MATTE TIN OVER BASE PLATING
- 4 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN
- 5 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE
- 6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



TOP SURFACE OF DAUGHTER CARD



6469183-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 25 JUL 2004 S. J. MAGARO		TE Connectivity	
DIMENSIONS:		CHK 25 JUL 2004 R. A. PATTERSON		NAME	
mm		APVD		PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		APPLICATION SPEC	
9 PLC ±		APVD		SIZE CAGE CODE DRAWING NO	
1 PLC ±		APVD		RESTRICTED TO	
3 PLC ±		APVD		A100779C-6469183	
5 PLC ±		APVD		SCALE 6:1 SHEET 1 OF 1 REV A	
4 PLC ±		APVD		CUSTOMER DRAWING	
ANGLES ±		APVD			
FINISH		APVD			