

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

— , — *

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

AF

50

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

APVD



R

REVISÉD PER ECR-11-018063


21DEC11

KH

	PD
--	----



SECTION X—X
SCALE 8:1



1 CONTINUOUS STRIP ON REELS.

△ 2 FOREIGN PRODUCTION ONLY.


4 MATING TAB THK IS .032±.001.

5 WIRE SIZE IS #18-#12 AWG

6 INSULATION RANGE IS
.110—.210 DIA.

7 PRELIMINARY – NOT FOR PRODUCTION

.000150 MIN NICKEL	T2 STEEL	 42742-5
PRE-TIN	4M BRASS	 42742-3
TIN	4M BRASS	42742-2
—	4M BRASS	42742-1
FINISH	MATERIAL	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH		1/23/91		TE Connectivity						
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK MS FEHER		1/24/93		NAME RECEPTACLE, FASTON, TM FLAG, .250 SERIES				
				APVD J GILLESPIE		1/24/93						
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± -		PRODUCT SPEC		—						
				APPLICATION SPEC		—						
				WEIGHT		—						
MATERIAL 4M BRASS		FINISH SEE TABLE		A3		00779		C-42742		RESTRICTED T —		
CUSTOMER DRAWING								SHEET 4.1		SHEET 1 OF 1		REV R