

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	SID	18/6/12	AMU	18/6/12		02/7/12

Specifications:

Current Rating	: 1 A ac / dc
Voltage Rating	: 30 V ac / dc
Maximum Contact Resistance	: 20 mΩ
Minimum Insulation Resistance	: 1,000 MΩ
Withstanding Voltage	: 500 V ac / minute
Operating Temperature Range	: -40°C to +105°C




Material and Finish

Insulator	: PBT, black
Contact	: Copper alloy
Finish	: Selective gold plated

Specifications Table

Positions	A	Part Number
10	18	1565522
14	23.08	1565523
16	25.62	1565524
20	30.74	1565525
26	38.32	1565526
34	48.48	1565528
40	56.1	1565529
50	68.8	1565530



PCB Layout

Dimensions : Millimetres

www.element14.com
www.farnell.com
www.newark.com

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

SID

CHECKED BY:

AMU

APPROVED BY:

DATE:

18/06/12

DATE:

18/06/12

DATE:

02/07/12

DRAWING TITLE:

2.54 mm IDC Plug DIP Type Connector

 SIZE
A

DWG NO.

M10002635

SCALE: NTS

U.O.M.: mm

 ELECTRONIC FILE
4403-XX(PC0204)_DWG

 REV
A

SHEET: 1 OF 1