

1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.

CM 00

CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN-LEAD ON SOLDER TAIL END.

REVISIONS

DESCRIPTION


Y1 REVISED PER ECO-11-004587

11MAR11 RK HMF

CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.

DIMENSIONS IN BRACKETS ARE IN INCHES.

CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.



PHOSPHOR BRONZE, GOLD 6	NYLON, UL94V—2 NATURAL	350428-4
PHOSPHOR BRONZE, GOLD 3	NYLON, UL94V—2 NATURAL	350428-2
PHOSPHOR BRONZE, PRE-TIN	NYLON, UL94V—2 NATURAL	350428-1
PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24JUN2003 S. CARPENTER CHK 24JUN2003 S. RIDGILL	-	TE Connectivity				
	DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±	APVD 24JUN2003 S. RIDGILL PRODUCT SPEC	NAME		PIN HEADER ASSEM 2 CIRCUIT	MBLY,	
		1 PLC ± 2 PLC ± 0.13 [.005] 3 PLC ± 4 PLC ± ANGLES ± 0'30'	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO
	MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	A1	00779	C -350428		
		CUSTOMER DRAWING		SCALE 5.1 SHE	EET 1 OF 1	REV V 1		

METRIC