




HONEYWELL PART NUMBER
2SX1-T
PRODUCT CODE VDC0150

REV	DOCUMENT	CHANGED BY	CHECK
8	0038447	SS 28MAR08	BLR




PLASTIC PLUNGER



- NOTES
- ⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188 ± .002 CENTERS
 - 2-TERMINALS ARE PLATED FOR SOLDERING
 - 3-SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.	SR-8881
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	SPK	04FEB08	Honeywell			
OPERATING FORCE — — — — 3 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	04FEB08				
RELEASE FORCE— — — — — 1 OZ MIN		28 VOLTS DC RATING			0.030 0.015 0.005		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC			
DIFFERENTIAL TRAVEL— — — .005 MAX			SEA LEVEL	50,000 FT									
OVERTRAVEL — — — — — .004 MIN		MAXIMUM INRUSH 24 AMP			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV	
APPROVALS	KEMA, CE	7A 250V~ T125 5E4 						B	I	2SX1-T		8	
	UL, CSA	7A 250 VAC  BRAND L7						SCALE - WEIGHT:.003 LB MAX SHEET 1 OF 1					