

CUSTOMER DRAWING





		PRODUCT DIMENSION				CONDUCTOR		MASS	
PART	COLOR CODE	I.D. (A)		Cut Length (B)		Wire O.D. (Note*)		KG/1000 pieces	
DESCRIPTION		Adhesive ± .05 (.002)	Sleeve ± .05 (.002)	Adhesive ±1 .5 (.06)	Sleeve ±1 .5 (.06)	Min	Max	Min	Max
D-150-C-11	Green	1.11 (.044)	2.29 (.090)	21.75 (.86)	19.05 (.75)	0.80 (.031)	1.10 (.043)	0.165	0.202
D-150-C-12	Red	1.68 (.066)	2.74 (.108)	21.75 (.86)	19.05 (.75)	1.10 (.043)	1.50 (.059)	0.198	0.242
D-150-C-13	Blue	2.13 (.084)	3.43 (.135)	21.75 (.86)	19.05 (.75)	1.50 (.059)	2.30 (.090)	0.261	0.319
D-150-C-14	Yellow	3.34 (.133)	4.80 (.189)	21.75 (.86)	19.05 (.75)	2.30 (.090)	2.80 (.110)	0.332	0.405

MATERIALS

- 1. MELTABLE ADHESIVES: Environment resistant modified thermoplastic fluoroelastomer. Color coded
- 2. OUTER SLEEVE: Heat-shrinkable, transparent, radiation cross-linked modified fluoropolymer. Color coded

APPLICATION

- 1. These parts are designed to provide an environment resistant to repair damaged primary wire that have a radial crack up to 360 degrees, nicks/scrapes not longer than ¼" on the insulation rated for 135°C minimum and no damage to wire conductor. For insulations procedures refer to RPIP 1101.
- Install using Tyco Electronics approved convection or infrared heating tools in accordance with Tyco Electronics. When installed
 with approved convection or infrared heating tools, assemblies will meet the performance requirements of TE D-6201 spec.
 Infrared tools are not recommended for use with black cable jackets.
- 3 Temperature range: -65° C to +180° C. Product will withstand continuous temperature of 150° C for a period of 500 hours, and continuous temperature of 180° C for a period of 168 hours.

NOTE*: If the O.D. of wire is out of the range that is specified in Table, use the next size of C-Wrap up or down.



=	ETE	TE Conne	ectivity	SIDE ENTRY REPAIR SLEEVE IMMERSION RESISTANT, 150 DEG C, ROHS COMPLIANT C-WRAP					
millimeters.[Inches	pecified dimensions s dimensions are sho	wn in brackets]	Raychem Devices	DOCUMENT NO.:	D-150-C-1X				
TOLERANCES: 0.00 ± 0.02 MM 0.0 ± 0.2 MM 0 ± 0.5 MM	ANGLES: ± 0°30' ROUGHNESS IN MICRON			REV:		DATE: March 14, 2013			
PREPARED BY: TNGUYEN	CAGE CODE: 06090	ECO NUMI ECO	BER: D-13-004675	SCALE: NTS		SIZE:	SHEET: 1 of 1		