

Customer Information Sheet

DRAWING No.: S1791-42R

SHEET 2 OF 2

IF IN DOUBT - ASK





(C)

NOT TO SCALE

THIRD ANGLE PROJECTION




ALL DIMENSIONS IN mm

TAPE DIMENSIONS




REEL DETAILS


RECOMMENDED PAD LAYOUT



SINGLE COMPONENT DRAWINGS



- NOTES:
1. QUANTITY PER REEL = 2000
 2. THIS PRODUCT IS TAPED AND REELED IN ACCORDANCE WITH EIA-481 (ELECTRONIC INDUSTRIES ASSOCIATION).
 3. AREA FOR GOLD PLATE.



REELING DIRECTION

COMPONENT SPECIFICATION

MATERIAL = TITANIUM COPPER ALLOY,
0.15±0.01mm THICK

FINISH = 0.76µ-1.27µ NICKEL, 0.05µ MIN FLASH
ON CONTACT AND FOOT AREA.

RECOMMENDED WORKING HEIGHT = 3.00mm / MIN FORCE = 1.0N

MINIMUM WORKING HEIGHT = 2.00mm / MAX FORCE = 4.0N

MAXIMUM PERMANENT SET = 0.20mm

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:

S1791-42 EMI SHIELD FINGER
IN TAPE AND REEL

DRAWING NUMBER:

S1791-42R

SHT

2 OF 2

CP	4	03.03.10	10687
NAME	ISS.	DATE	C/NOTE
APPROVED: C.PENROSE			
CHECKED: R.ADDE			
DRAWN: N. CODLING			
CUSTOMER REF.:			
ASSEMBLY DRG:			