

Customer Information Sheet

DRAWING No.: M50-90XXX42

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

**SPECIFICATIONS:****MATERIAL:**

MOULDINGS = PBT 30% G/F, UL94V-0, BLACK

CONTACT = PHOSPHOR BRONZE

FINISH:**CONTACTS =**

M50-330XX42 = 0.015-0.02µ MIN GOLD ON CONTACTS, 2.54µ MIN 100% TIN ON TAILS, OVER 0.76-2.03µ NICKEL

M50-380XX42 = 0.015-0.02µ MIN GOLD ON CONTACTS, OVER 0.76-2.03µ NICKEL

ELECTRICAL:

CONTACT RESISTANCE = 1.0Ω MAX

WORKING VOLTAGE = 300V DC MIN

INSULATION RESISTANCE = 5MΩ MIN

MECHANICAL:

INSERTION FORCE = 1.0N MAX PER CONTACT

WITHDRAWAL FORCE = 0.14N MIN PER CONTACT

ENVIRONMENTAL:

TEMPERATURE RANGE = -20°C TO +105°C

PACKING:

BAG

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C029XX (LATEST ISSUE)

NOTES:

- CONNECTORS M50-330XX42 & M50-380XX42, AS WELL AS CABLE, ARE RoHS COMPLIANT.
- FOR CONNECTOR DETAILS SEE DRAWINGS M50-330XX42 & M50-380XX42.

SB	4	29.08.12	11800
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		S.FLOWER	
DRAWN:		R.ADDE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

PART No.	DIM 'A'	No. OF CONTACTS PER ROW
M50-901XX42	150	05, 10, 13, 17, 20, 25
M50-902XX42	300	05, 10, 13, 17, 20, 25

HARWINwww.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED**MATERIAL:**

SEE ABOVE

FINISH: SEE ABOVE**S/AREA:**mm²**TITLE:**1.27mm PITCH IDC
DIL SOCKET/PLUG
CABLE ASSEMBLY**DRAWING NUMBER:****M50-90XXX42**SHT
2
OF
2