







LOC		DIST		REVISES			
AD	00	P	LYR	DESCRIPTION	DATE	OWN	APVD
		B		REVISED PER ECO-11-025276	26DEC11	KH	DY

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A. SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.



RIGHT GUIDED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)




THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. K. SHOBER 26DEC11	 TE Connectivity			
DIMENSIONS:		CHK J. EABY 26DEC11				
mm		APVD J. EABY 26DEC11	NAME			
		PRODUCT SPEC	IMPACT, 4 PAIR, 10 COLUMN, HEADER			
		APPLICATION SPEC	RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH			
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	SEE TABLE	-	A1	100779	C=2007813	-
CUSTOMER DRAWING		SCALE		SHEET		OF
		6:1		1		2
				REV		B

LOC		DIST		REVISIONS						
AD	00	P	LTR	DESCRIPTION			DATE	DWN	APVD	
		-		SEE SHEET 1			-	-	-	


	H	5.5	8-2007813-6
	H	4.9	8-2007813-5
	H	4.5	8-2007813-4
	H	5.5	8-2007813-3
	H	4.9	8-2007813-2
	H	4.5	8-2007813-1
	G	5.5	7-2007813-6
	G	4.9	7-2007813-5
	G	4.5	7-2007813-4
	G	5.5	7-2007813-3
	G	4.9	7-2007813-2
	G	4.5	7-2007813-1
	F	5.5	6-2007813-6
	F	4.9	6-2007813-5
	F	4.5	6-2007813-4
	F	5.5	6-2007813-3
	F	4.9	6-2007813-2
	F	4.5	6-2007813-1
	E	5.5	5-2007813-6
	E	4.9	5-2007813-5
	E	4.5	5-2007813-4
	E	5.5	5-2007813-3
	E	4.9	5-2007813-2
	E	4.5	5-2007813-1
	D	5.5	4-2007813-6
	D	4.9	4-2007813-5
	D	4.5	4-2007813-4
	D	5.5	4-2007813-3
	D	4.9	4-2007813-2
	D	4.5	4-2007813-1
	C	5.5	3-2007813-6
	C	4.9	3-2007813-5
	C	4.5	3-2007813-4
	C	5.5	3-2007813-3
	C	4.9	3-2007813-2
	C	4.5	3-2007813-1
	B	5.5	2-2007813-6
	B	4.9	2-2007813-5
	B	4.5	2-2007813-4
	B	5.5	2-2007813-3
	B	4.9	2-2007813-2
	B	4.5	2-2007813-1
	A	5.5	1-2007813-6
	A	4.9	1-2007813-5
	A	4.5	1-2007813-4
	A	5.5	1-2007813-3
	A	4.9	1-2007813-2
	A	4.5	1-2007813-1
	-	5.5	2007813-6
	-	4.9	2007813-5
	-	4.5	2007813-4
	-	5.5	2007813-3
	-	4.9	2007813-2
	-	4.5	2007813-1
FINISH	KEY POSITION	DIM M	PART NUMBER


REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY


KEY POSITION
CHART





NONE


A


E


B


F

C

G

D

H

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 26DEC11	 TE Connectivity		
DIMENSIONS: mm		CHK J. EABY 26DEC11			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME IMPACT, 4 PAIR, 10 COLUMN, HEADER RIGHT GUIDED, OPEN END WALL SIGNAL MODULE, 0.39 PTH	
		9 PLC ± 3 PLC ±0.25 5 PLC ±0.13 4 PLC ± ANGLES ±		PRODUCT SPEC	
		FINISH SEE TABLE		APPLICATION SPEC	
MATERIAL -		WEIGHT -		SIZE A100779	
		CUSTOMER DRAWING		CAGE CODE C=2007813	
		SCALE 5:1		SHEET 2 OF 2	
				REV B	