





LOC		DIST		REVISONS			
AD	00	P	LYR	DESCRIPTION	DATE	OWN	APVD
		B		REVISED PER ECO-11-025276	26DEC11	KH	DY

- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.
4. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- 5 FOR GROUNDED GUIDE PIN USE Ø3.56±0.08 PTH,
Ø3.66 DRILL, AND Ø6.5 PAD.
6. KEYING PIN SHOWN IN POSITION A. SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.



LEFT GUIDIED
BACKPLANE HOLE PATTERN
(CONNECTOR SIDE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J. K. SHOBER 13JAN2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 13JAN2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. EABY 13JAN2011	NAME	
mm		PRODUCT SPEC	IMPACT, 4 PAIR, 16 COLUMN, HEADER	
9 PLC ±.1		APPLICATION SPEC	LEFT GUIDED, RIGHT END WALL	
1 PLC ±0.25		WEIGHT	SIGNAL MODULE, 0.39 PTH	
2 PLC ±0.13		SIZE	A100779C=2007827	
3 PLC ±.1		CAGE CODE	DRAWING NO	
4 PLC ±.1		RESTRICTED TO	-	
ANGLES ±.1		CUSTOMER DRAWING	SCALE 6:1 SHEET 1 OF 2 REV B	
FINISH SEE TABLE				

LOC		DIST		REVISIONS						
AD		00		REV	LYR	DESCRIPTION	DATE	DWN	APVD	
				-	-	SEE SHEET 1	-	-	-	

	H	5.5	8-2007827-6
	H	4.9	8-2007827-5
	H	4.5	8-2007827-4
	H	5.5	8-2007827-3
	H	4.9	8-2007827-2
	H	4.5	8-2007827-1
	G	5.5	7-2007827-6
	G	4.9	7-2007827-5
	G	4.5	7-2007827-4
	G	5.5	7-2007827-3
	G	4.9	7-2007827-2
	G	4.5	7-2007827-1
	F	5.5	6-2007827-6
	F	4.9	6-2007827-5
	F	4.5	6-2007827-4
	F	5.5	6-2007827-3
	F	4.9	6-2007827-2
	F	4.5	6-2007827-1
	E	5.5	5-2007827-6
	E	4.9	5-2007827-5
	E	4.5	5-2007827-4
	E	5.5	5-2007827-3
	E	4.9	5-2007827-2
	E	4.5	5-2007827-1
	D	5.5	4-2007827-6
	D	4.9	4-2007827-5
	D	4.5	4-2007827-4
	D	5.5	4-2007827-3
	D	4.9	4-2007827-2
	D	4.5	4-2007827-1
	C	5.5	3-2007827-6
	C	4.9	3-2007827-5
	C	4.5	3-2007827-4
	C	5.5	3-2007827-3
	C	4.9	3-2007827-2
	C	4.5	3-2007827-1
	B	5.5	2-2007827-6
	B	4.9	2-2007827-5
	B	4.5	2-2007827-4
	B	5.5	2-2007827-3
	B	4.9	2-2007827-2
	B	4.5	2-2007827-1
	A	5.5	1-2007827-6
	A	4.9	1-2007827-5
	A	4.5	1-2007827-4
	A	5.5	1-2007827-3
	A	4.9	1-2007827-2
	A	4.5	1-2007827-1
	-	5.5	2007827-6
	-	4.9	2007827-5
	-	4.5	2007827-4
	-	5.5	2007827-3
	-	4.9	2007827-2
	-	4.5	2007827-1
FINISH	KEY POSITION	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

KEY POSITION
CHART

NONE

A

E

B

F

C

G

D

H

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 13JAN2011	TE Connectivity	
DIMENSIONS:		CHK J. EABY 13JAN2011	NAME	
mm		APVD J. EABY 13JAN2011	IMPACT, 4 PAIR, 16 COLUMN, HEADER LEFT GUIDED, RIGHT END WALL SIGNAL MODULE, 0.39 PTH	
9 PLC ±.0 3 PLC ±0.25 3 PLC ±0.13 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH SEE TABLE		PRODUCT SPEC		SIZE
		APPLICATION SPEC		CAGE CODE
MATERIAL		WEIGHT		DRAWING NO
-		-		A100779C=2007827
		CUSTOMER DRAWING		RESTRICTED TO
		SCALE 5:1		SHEET 2 OF 2
				REV B