


THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION



© COPYRIGHT

By -

ALL RIGHTS RESERVED




20.32

 8.13 ± 0.25 


20.70 MAX

SEE DETAIL A

1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSION REPRESENTS POTENTIAL MAXIMUM GROWTH DUE TO MOISTURE ABSORPTION.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION.
NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




DETAIL A
OPTIONAL CONSTRUCTIONS




6.35	.250	—	—
4.45	.175	27.43	1.080
2.79	.110	26.43	1.041
2.54	.100	25.91	1.020
2.29	.090	20.70	.815
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.13	.320
0.13	.005	6.99	.275
MM	IN	MM	IN

CONVERSION TABLE

4805 (3/11)

△ 6 25.91^{+0.13}_{-0.25}

 27.43 ± 0.38 

RECOMMENDED PANEL CUT OUT






9 9 OBSELETE 9 SUPERSEDED BY 1-480707-0 9 OBSELETE	BLACK	1-480707-9
	GRAY	1-480707-8
	BLUE	1-480707-6
	GREEN	1-480707-5
	YELLOW	1-480707-4
	ORANGE	1-480707-3
	RED	1-480707-2
	BROWN	1-480707-1
	NATURAL	1-480707-0
	COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 29JUL04 K. WHITAKER CHK 29JUL04 S. RIDGILL APD 29JUL04 S. RIDGILL		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 3 PLC ± — 4 ANGLES ± 0°30'		NAME CAP. 9 CIRCUIT. UNIVERSAL MATE-N-LOK(TM)	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE A1	
MATERIAL NYLON, UL94V-2		FINISH —		CAGE CODE 00779	
		WEIGHT —		DRAWING NO C=480707	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 2 REV. A	


METRIC

LOC	DIST	REVISIONS				
CM	00	REV	LTR	DESCRIPTION	DATE	DWN
		—		SEE SHEET 1	—	—

1. STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE);CLARIFICATION MARKS UNDER THE 6 & 9.
2. CHARACTERS TO BE STAMPED ON HOUSING IN A MANNER AS TO BE READ FROM WIRE END ONLY.
3. VIOLET,BLACK,BROWN,AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



5.08	.200	—	—
4.70	.185	27.43	1.080
3.18	.125	25.91	1.020
0.38	.015	20.70	.815
0.25	.010	20.32	.800
0.13	.005	8.13	.320
MM	IN	MM	IN
CONVERSION TABLE			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	29JUL04	 TE Connectivity	
		CHK S. RIDGILL	29JUL04		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0. PLC ± —		CAP, 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
		1. PLC ± —			
		2. PLC ± 0.13			
		3. PLC ± —			
4. PLC ± —		APPLICATION SPEC		SIZE	
ANGLES		± 0°30'		CAGE CODE	
FINISH		—		DRAWING NO	
MATERIAL NYLON, UL94V-2		WEIGHT —		RESTRICTED TO	
		CUSTOMER DRAWING		A1 00779 C=480707	
				SCALE 4:1	
				SHEET 2 OF 2	
				REV AK2	