






# M-7145 4




CAT. NO.	CONFIGURATION	RATING	UL	CSA
HBL5279C	NEMA 5-15R 	15A. 125V.	YES	YES
HBL5379C	NEMA 5-20R 	20A. 125V.	YES	YES
HBL5479C	NEMA 6-20R 	20A. 250V.	YES	YES
HBL5679C	NEMA 6-15R 	15A. 250V.	YES	YES

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	NYLON	NATURAL
RETAINER	POLYCARBONATE	CLEAR
CASING	NYLON	NATURAL
WIRE CLAMP	.062 CRS	NICKEL PL
BINDING PLATE	.031	
CONTACT SPRING	BRONZE	
INNER SPRING	.031	
	BRONZE	
BINDING SCREW	BRASS	*
GROUND HEX HEAD BINDING SCREW	BRASS	GREEN
MTG. SCREWS	BRASS	NICKEL PL
ASSEM FASTENERS	STEEL	ZINC PL

\*WHITE FINISH ON NEUTRAL PARTS WHEN USED

REV	DESCRIPTION	APP	DATE
4	IN LIST OF PARTS, "POLYCARBONATE WAS "LEXAN"; PER DCN #8996. MN	CJC CJC	2/18/02
3	REMOVED "-" FROM ALL CATALOGS ADDED CSA LOGO TO HBL5379C & HBL549C, CHANGED SCREW TO TRI-DRIVE PER DCN #7773. AMZ	DB	7/20/00
2	TABLE UPDATED; "ALL SCREWS..." ADDED; AGENCY LISTED..." ADDED PER DCN #2940 RCM	JEZ	8/1/94
1	"X" REMOVED PER DCN #1906 RCM	VFL	7/13/93
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE INSULGRIP  2 POLE 3 WIRE GROUNDING STRAIGHT BLADE FLANGED OUTLETS

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS $\pm 1/64$	DR. BY RCM	APP. BY VFL
DECIMALS $\pm .005$	TR. BY	SCALE $\neq$
ANGLES $\pm 2^\circ$	CHK'D BY ZIMM	DATE 7/13/93

DIMENSION SHEET FOR CAT. NO. M-7145  
 SEE TABLE  
 REPAIRABLE  NON-REPAIRABLE   
 B  
 M-7145  
 4