




- 1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 6 SUPERSEDED BY 350787-3



3-DIMENSIONAL MODEL
NTS

6	PHOSPHOR BRONZE, GOLD Δ 5		NYLON,UL94V-0,WHITE		350787-3
	PHOSPHOR BRONZE, GOLD Δ 2		NYLON,UL94V-0,WHITE		350787-2
	PHOSPHOR BRONZE, PRE-TIN		NYLON,UL94V-0,WHITE		350787-1
PIN CONTACT MATERIAL AND FINISH			HOUSING MATERIAL		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			OWN B. LEWIS 8-20-98		 TE Connectivity	
			CHK R. SWING 8-20-98			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV M. TRULL 8-20-98		NAME
		0 PLC ± -		PIN SPEC		PIN HEADER ASSEMBLY, 2 CIRCUIT UNIVERSAL MATE-N-LOK™
		1 PLC ± -		—		
		2 PLC ± 0.13 [.005]		—		
		3 PLC ± -		APPLICATION SPEC		
		4 PLC ± -		—		
ANGLES ± ± 0°30'				SIZE		CAGE CODE
MATERIAL		FINISH		WEIGHT		DRAWING NO
SEE TABLE		SEE TABLE		—		A1 00779
CUSTOMER DRAWING				SCALE 5:1		SHEET 1 OF 1
						REV P1