



ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	PM3-XXX	LED Holder, Panel Mount, Press Fit, (3mm) PM3 (Standard LED), PM3-5V (5V LED), & PM3-12V (12V LED)
2	1	3XXX-S	T1 (3mm) Shouldered LED, See Following Pages
3	1	BWS24-1061-RD	24AWG Wire Lead U.L. 1061, Red
4	1	BWS24-1061-BK	24AWG Wire Lead U.L. 1061, Black

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	02/05/08	M. C.
B	Updated Bi-Color Polarity	09/09/08	M. C.
C	LED Spec Update	03/22/10	T. Y.
D	Bi-Color LED Spec Update	06/24/11	T. Y.
E	Updated LED Offering	05/01/12	T. Y.
F	Updated BOM Item 1	11/12/12	T. Y.



EXAMPLE:
PM3RDW6.5*
 Series | LED Color, Lens Appearance | Wire Length in inches

BI-COLOR POLARITY		
LED P/N	(1) Cathode	(2) Cathode
3BC	Green	Red
3BC-Y/G	Green	Yellow
3BC-R/Y	Yellow	Red
3BC-A/G	Green	Amber





ABSOLUTE MAXIMUM RATINGS (Ta = 25°C)

REVERSE VOLTAGE	5V
REVERSE CURRENT (VR=5V)	100µA
OPERATING TEMPERATURE RANGE	-25°C ~ 85°C
STORAGE TEMPERATURE	-30°C ~ 100°C
LEAD SOLDERING TEMPERATURE (1/16" FROM BODY)	260°C for 5 Seconds

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ±.1	X° ± 1°	TITLE: STD PANEL MOUNT INDICATORS W/ WIRES PART NO: PM3XXXWX.X REVISION: F	
.XX ±.02			
.XXX ±.010			
DESIGNED: Raffy Paje	DATE: 02/05/08	CAGE CODE : 32559	SHEET # 1 OF 4
CHECKED: T. Yin	DATE: 02/05/08	CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.	



REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET#1.		

LED Assy. No.	Chip			Lens Appearance	Electro-Optical Data @ 20mA				Viewing Angle 2 θ ½ (Deg)	LED P/N	
	Material	Peak Wave Length	Emitted Color		If (mA)	Vf (V)		Iv (mcd)			
						MAX	TYP	MAX			TYP
PM3BWCWX.X	GaN/SiC	430	BLUE	WATER CLEAR	25	4	4.5	25	30	3BWC-S	
PM3BWDWX.X	GaN/SiC	430	BLUE	DIFFUSED	25	4	4.5	10	40	3BWD-S	
PM3BWTWX.X	GaN/SiC	430	BLUE	TINTED	25	4	4.5	25	30	3BWT-S	
PM3GCWX.X	GaP/GaP	568	GREEN	WATER CLEAR	30	2.1	2.8	40	30	3GC-S	
PM3GDWX.X	GaP/GaP	568	GREEN	DIFFUSED	30	2.1	2.8	25	40	3GD-S	
PM3GTWX.X	GaP/GaP	568	GREEN	TINTED	30	2.1	2.8	40	30	3GT-S	
PM3PGCWX.X	GaP/GaP	555	PURE GREEN	WATER CLEAR	30	2.2	2.8	10	30	3PGC-S	
PM3PGDWX.X	GaP/GaP	555	PURE GREEN	DIFFUSED	30	2.2	2.8	5	40	3PGD-S	
PM3PGTWX.X	GaP/GaP	555	PURE GREEN	TINTED	30	2.2	2.8	10	30	3PGT-S	
PM3YCWX.X	GaAsP/GaP	590	YELLOW	WATER CLEAR	30	2	2.8	40	30	3YC-S	
PM3YDWX.X	GaAsP/GaP	590	YELLOW	DIFFUSED	30	2	2.8	20	40	3YD-S	
PM3YTWX.X	GaAsP/GaP	590	YELLOW	TINTED	30	2	2.8	40	30	3YT-S	
PM3ACWX.X	GaAsP/GaP	605	AMBER	WATER CLEAR	30	2	2.8	40	30	3AC-S	
PM3ADWX.X	GaAsP/GaP	605	AMBER	DIFFUSED	30	2	2.8	25	40	3AD-S	
PM3ATWX.X	GaAsP/GaP	605	AMBER	TINTED	30	2	2.8	40	30	3AT-S	
PM3HCWX.X	GaAsP/GaP	625	HE RED	WATER CLEAR	30	2	2.8	50	30	3HC-S	
PM3HDWX.X	GaAsP/GaP	625	HE RED	DIFFUSED	30	2	2.8	30	40	3HD-S	
PM3HTWX.X	GaAsP/GaP	625	HE RED	TINTED	30	2	2.8	50	30	3HT-S	
PM3RCWX.X	GaP/GaP	700	RED	WATER CLEAR	20	2.1	2.8	2.5	30	3RC-S	
PM3RDWX.X	GaP/GaP	700	RED	DIFFUSED	20	2.1	2.8	2	40	3RD-S	
PM3RTWX.X	GaP/GaP	700	RED	TINTED	20	2.1	2.8	2.5	30	3RT-S	
PM3BC-A/GWX.X	GaAsP/GaP	605	AMBER	DIFFUSED	30	2.0	2.8	6	45	3BC-A/G	
	GaP/GaP	568	GREEN		30	2.1	2.8	6			
PM3BCWX.X	GaAsP/GaP	625	RED	DIFFUSED	30	2.0	2.8	6	45	3BC	
	GaP/GaP	568	GREEN		30	2.1	2.8	6			
PM3BC-R/YWX.X	GaAsP/GaP	625	RED	DIFFUSED	30	2.0	2.8	6	45	3BC-R/Y	
	GaAsP/GaP	590	YELLOW		30	2.0	2.8	4			
PM3BC-Y/GWX.X	GaAsP/GaP	590	YELLOW	DIFFUSED	30	2.0	2.8	4	45	3BC-Y/G	
	GaP/GaP	568	GREEN		30	2.1	2.8	6			

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) ±10% ALL VALUES		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
ANGULAR X° ± 5°			
		TITLE: STD PANEL MOUNT INDICATORS W/ WIRES	
DESIGNED: Raffy Paje	DATE: 02/05/08	PART NO: PM3XXXWX.X	REVISION: F
CHECKED: T. Yln	DATE: 02/05/08	CAGE CODE : 32559	SHEET # 2 OF 4
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET#1.		



LED Assy. No.	Chip			Lens Appearance	Electro-Optical Data @ 20mA				Viewing Angle 2 θ ½ (Deg)	LED P/N	
	Material	Peak Wave Length	Emitted Color		If (mA)	Vf (V)		Iv (mcd)			
						MAX	TYP	MAX			TYP
PM3UBWCWX.X	GaN/SiC	470	BLUE	WATER CLEAR	30	4	4.5	400	30	3UBWC-0.6K	
PM3SGCWX.X	GaP/GaP	568	GREEN	WATER CLEAR	30	2.1	2.8	50	30	3SGC-S	
PM3SGDWX.X	GaP/GaP	568	GREEN	DIFFUSED	30	2.1	2.8	30	40	3SGD-S	
PM3SGTWX.X	GaP/GaP	568	GREEN	TINTED	30	2.1	2.8	50	30	3SGT-S	
PM3SYCWX.X	GaAsP/GaP	590	YELLOW	WATER CLEAR	30	2.0	2.8	50	30	3SYC-S	
PM3SYDWX.X	GaAsP/GaP	590	YELLOW	DIFFUSED	30	2.0	2.8	30	40	3SYD-S	
PM3SYTWX.X	GaAsP/GaP	590	YELLOW	TINTED	30	2.0	2.8	50	30	3SYT-S	
PM3SACWX.X	AlGaInP	605	AMBER	WATER CLEAR	30	1.8	2.4	300	30	3SAC-S	
PM3SADWX.X	AlGaInP	605	AMBER	DIFFUSED	30	1.8	2.4	100	40	3SAD-S	
PM3SATWX.X	AlGaInP	605	AMBER	TINTED	30	1.8	2.4	300	30	3SAT-S	
PM3SRCWX.X	GaAlAs/GaAs	645	SUPER RED	WATER CLEAR	30	1.7	2.4	60	30	3SRC-S	
PM3SRDWX.X	GaAlAs/GaAs	645	SUPER RED	DIFFUSED	30	1.7	2.4	40	40	3SRD-S	
PM3SRTWX.X	GaAlAs/GaAs	645	SUPER RED	TINTED	30	1.7	2.4	60	30	3SRT-S	
PM3UGCWX.X	AlGaInP	570	GREEN	WATER CLEAR	30	2.1	2.4	200	30	3UGC-S	
PM3SUGCWX.X	AlGaInP	570	GREEN	WATER CLEAR	30	2.1	2.4	300	30	3SUGC-S	
PM3UYCWX.X	AlGaInP	590	YELLOW	WATER CLEAR	30	2.0	2.4	300	30	3UYC-S	
PM3SUYCWX.X	AlGaInP	590	YELLOW	WATER CLEAR	30	2.0	2.4	400	30	3SUYC-S	
PM3UUYCWX.X	AlGaInP	590	YELLOW	WATER CLEAR	30	2.0	2.4	600	30	3UUYC-S	
PM3UOCWX.X	AlGaInP	625	ORANGE	WATER CLEAR	30	1.8	2.4	300	30	3UOC-S	
PM3SUOCWX.X	AlGaInP	625	ORANGE	WATER CLEAR	30	1.8	2.4	400	30	3SUOC-S	
PM3URCWX.X	GaAlAs/GaAs	645	RED	WATER CLEAR	30	1.7	2.4	200	30	3URC-S	
PM3SURCWX.X	AlGaInP	640	RED	WATER CLEAR	30	1.8	2.4	200	30	3SURC-S	
PM3UWCWX.X	InGaN/Sapphire	6500K	WHITE	WATER CLEAR	30	3.4	3.8	1000	30	3UWC1.030C	

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) ±10% ALL VALUES		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
ANGULAR X° ± 5°			
		TITLE: STD PANEL MOUNT INDICATORS W/ WIRES	
		DESIGNED: Raffy Paje	DATE: 02/05/08
CHECKED: T. Yin		DATE: 02/05/08	CAGE CODE : 32559 SHEET # 3 OF 4 CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.

REV.	DESCRIPTION	DATE	APPROVED
	SEE SHEET#1.		

LED Assy. No.	Chip			Lens Appearance	Absolute Max. Ratings			Electro-Optical Data @ 2mA			Viewing Angle 2θ ½ (Deg)	LED P/N
	Material	Peak Wave Length λp(nm)	Emitted Color		Pd (mW)	If (mA)	Peak If(mA)	Vf (V)		Iv (mcd)		
								TYP	MAX	TYP		
PM3BVDLWX.X	GaN/siC	430	BLUE	DIFFUSED	20	7	-	3.8	4.2	2.5	40	3BVDL-S
PM3GDLWX.X	GaP/GaP	568	GREEN	DIFFUSED	10	7	-	2.1	2.6	2.0	40	3GDL-S
PM3PGDLWX.X	GaP/GaP	555	PURE GREEN	DIFFUSED	10	7	-	2.1	2.6	0.2	40	3PGDL-S
PM3YDLWX.X	GaAsP/GaP	590	YELLOW	DIFFUSED	10	7	-	2.0	2.6	2.0	40	3YDL-S
PM3ADLWX.X	GaAsP/GaP	605	AMBER	DIFFUSED	10	7	-	2.0	2.6	4.0	40	3ADL-S
PM3HDLWX.X	GaAsP/GaP	625	HE RED	DIFFUSED	10	7	-	2.0	2.6	2.5	40	3HDL-S
PM3RDLWX.X	GaP/GaP	700	RED	DIFFUSED	10	7	-	2.1	2.6	0.5	40	3RDL-S
PM3SRDLWX.X	GaAlAs/GaAs	645	RED	DIFFUSED	10	7	-	2.0	-	8.0	40	3SRDL-S

Assembly P/N	Peak Wave Length λp(nm)	Emitted Color	Lens Appearance	Electro-Optical Data				Viewing Angle 2θ 1/2 (Deg)	LED P/N
				If (mA)	Vf (V)		Iv (mcd)		
					MAX	TYP	MAX		
5 Volt				Data @ 5V					
PM3BWD5VWX.X	430	BLUE	DIFFUSED	-	-	5	10	35	3BWD5V-S
PM3GC5VWX.X	568	GREEN	WATER CLEAR	-	-	5	40	20	3GC5V-S
PM3GD5VWX.X	568	GREEN	DIFFUSED	-	-	5	25	35	3GD5V-S
PM3GT5VWX.X	568	GREEN	TINTED	-	-	5	40	20	3GT5V-S
PM3AD5VWX.X	605	AMBER	DIFFUSED	-	-	5	25	35	3AD5V-S
PM3HD5VWX.X	625	HE RED	DIFFUSED	-	-	5	30	35	3HD5V-S
PM3RD5VWX.X	700	RED	DIFFUSED	-	-	5	2	35	3RD5V-S
PM3YD5VWX.X	590	YELLOW	DIFFUSED	-	-	5	20	35	3YD5V-S
12 Volt				Data @ 12V					
PM3GC12VWX.X	568	GREEN	WATER CLEAR	-	-	12	40	20	3GC12V-S
PM3GD12VWX.X	568	GREEN	DIFFUSED	-	-	12	25	35	2GD12V-S
PM3HC12VWX.X	625	HE RED	WATER CLEAR	-	-	12	50	20	3HC12V-S
PM3HD12VWX.X	625	HE RED	DIFFUSED	-	-	12	30	35	3HD12V-S
PM3RC12VWX.X	700	RED	WATER CLEAR	-	-	12	6	20	3RC12V-S
PM3RD12VWX.X	700	RED	DIFFUSED	-	-	12	2	35	3RD12V-S
PM3YC12VWX.X	590	YELLOW	WATER CLEAR	-	-	12	40	20	3YC12V-S
PM3YD12VWX.X	590	YELLOW	DIFFUSED	-	-	12	25	35	3YD12V-S

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED) ±10% ALL VALUES		 BIVAR [®] 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
ANGULAR X° ± 5°			
		TITLE: STD PANEL MOUNT INDICATORS W/ WIRES	
DESIGNED: Raffy Paje	DATE: 02/05/08	PART NO: PM3XXXWX.X	REVISION: F
CHECKED: T. Yin	DATE: 02/05/08	CAGE CODE : 32559	SHEET # 4 OF 4
CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING.			